

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
C2		REVISED PER ECR-14-001994	11FEB2014	A.Z	D.Z
D		REVISED PER ECR-19-009721	01JUL2019	M.G	D.Z








FIG 1  
RECOMMENDED PANEL OPENING DIMENSION



- 1 THIS HOUSING ACCEPTS TAB TERMINAL:  
TAB CONTACT: 177917-□ (#20-#16AWG)  
177916-□ (#26-#22AWG)
- 2 MATING CONN. P/N  
PLUG HSG: □-177903-□ (#20-#16AWG)  
REC CONTACT: 177915-□ (#20-#16AWG)  
177914-□ (#26-#22AWG)
- 3 APPLICABLE PLATE P/N: 177919-□
- 4 INSTRUCTION SHEET: 411-5638
- 5 APPLICABLE PANEL THICKNESS: 0.8~2.0(SEE FIG 1)
- 6 INSERT CONN. FROM PRESS DIRECTION SIDE FOR METAL PANEL.
- 7 EDGE OF THICKNESS WAY MUST NOT ROUND FOR MOLDED PANEL.
- 8 ALL PARTS MEET RTI ELECTRICAL RATING OF 105°C ACCORDING TO UL 1977.
- 9 MATERIAL: 6/6 NYLON UL94V-0
- 10 PART 5-177911-1 COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT)
- 11 SEE TABLE 1
- 12 GENERAL TOLERANCE:  
<10:±0.2  
10~30:±0.25,  
ANGLE:±3°



SECTION A-A



CIRCUIT NO.

TRADE MARK	MANUFACTURING PLACE
-AMP OR AMP	JAPAN
-+AMP OR AMP	CHINA
+AMP OR AMP	KOREA

9	NATURAL	5-177911-1
9	BLUE	177911-6
9	YELLOW	177911-4
9	NATURAL	177911-1
POS	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SUZUKI 09SEPT1993	TE Connectivity AMP POWER DBL LOCK CONN, 3.96mm PITCH (TRIPLE ROW) 9 Pos CAP HOUSING (PANEL MOUNT)
DIMENSIONS: mm		CHK M. SHINDO 09SEPT1993	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Y. KASHIWA 09SEPT1993	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH ±		PRODUCT SPEC 108-5410 APPLICATION SPEC 114-5175 WEIGHT -	
MATERIAL 9		CUSTOMER DRAWING	SIZE A200779 CAGE CODE C-177911 DRAWING NO. G-177911 RESTRICTED TO SCALE 5:1 SHEET 1 OF 1 REV D

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-177911-1](#)