

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT 2017 TE Connectivity ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
9		RIBS ADDED AT BOTH ENDS	08APR2019	HSR PS
10		RIB ADDED ON LATCH	17JUL2019	AY PS
11		OVERALL LENGTH UPDATED	13SEP2019	AY PS
12		REMOVED NOTE 5	19SEP2019	AY PS

Top view of the dual row housing showing dimensions: $E \pm 0.1 (10.1)$, 2 ± 0.08 TYP NON-CUMULATIVE, 4.00 , and 2 ± 0.08 TYP.

Side view of the housing showing dimensions: 8.5 , 4.3 , 6.7 ± 0.1 , and 4.7 .

NOTES:

- MATERIAL:
LCP BLACK, UL94 V0
- N = NUMBER OF POSITION PER HOUSING.
- HOUSING TO BE USED WITH CRIMP CONTACTS
2316113 (AWG 28-24/0.08-0.22 mm²) AND
2316114 (AWG 30-28/0.05-0.08 mm²)
- PACKAGING : BOX

Front view of the housing showing the center latch mechanism.

DUAL ROW HOUSING
CENTER LATCH VERSION,
1- -0 AS SHOWN

3D perspective view of the dual row housing with center latch.

SCALE 5:1

CENTERLINE AND POSITIONS UNDER THE LATCH

5-2316110-0	50.1	50
4-2316110-4	44.1	44
4-2316110-0	40.1	40
3-2316110-2	32.1	32
3-2316110-0	30.1	30
2-2316110-8	28.1	28
2-2316110-6	26.1	26
2-2316110-4	24.1	24
2-2316110-2	22.1	22
2-2316110-0	20.1	20
1-2316110-8	18.1	18
1-2316110-6	16.1	16
1-2316110-4	14.1	14
1-2316110-2	12.1	12
1-2316110-0	10.1	10
2316110-8	8.1	8
2316110-6	6.1	6
PART NO.	DIM "E"	N

THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.15 2 PLC ±0.10 3 PLC ± 4 PLC ± ANGLES ±2° FINISH	DWN RAKSHITH R NAYAK 06SEP2016 CHK PRASHANTH S 06SEP2016 APVD PRASHANTH S 06SEP2016 PRODUCT SPEC 108-64040-1 APPLICATION SPEC 114-32173 WEIGHT - CUSTOMER DRAWING	NAME AMPMODU 2mm, WTB, RECEPTACLE, HOUSING, CRIMP, DUAL ROW, CENTER LATCH SIZE A2 CAGE CODE 00779 DRAWING NO C-2316110 RESTRICTED TO - SCALE 10:1 SHEET 1 OF 1 REV 12
-------------------	---	---	--

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2316110-6](#)