





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - BY - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
B		REVISED PER ECO-12-018187	2NOV2012	CT	KH		



MATING FACE



- 1 FRONT & REAR INSULATORS: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.
 CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194
 REAR GROMMET & INTERFACIAL SEAL: FLUROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1.
- 2 PART TO BE MARKED WITH TE IDENTIFICATION, TE PART NO.
 AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.
- 3. THIS INSERT CONTAINS: 24 CAVITIES FOR SIZE 22 PIN CONTACTS
 1 CAVITY FOR SIZE 8 QUADRAX PIN CONTACTS.
- 4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIALL SA.

THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING

ENVIROMENTAL	GPRBE25QISB	1877568-1
REMARKS	DISCRIPTIVE PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	8NOV07	TE Connectivity NAME INSERT ASSEMBLY, SOCKET, ENVIRONMENTAL, ARRANGEMENT 25Q1, KEY B, GPRB					
DIMENSIONS:		CHK	8NOV07						
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	8NOV07						
mm		PRODUCT SPEC							
0 PLC ± 1 PLC ± 2 PLC ±0.05 3 PLC ± 4 PLC ± ANGLES ± FINISH		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL		WEIGHT		A2	00779	C-1877568			
MATERIAL		CUSTOMER DRAWING		SCALE	4:1	SHEET	OF	REV	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1877568-1](#)