





LOC		DIST		REVISIONS			
ES	00	P	LTN	DESCRIPTION	DATE	DWN	APVD
		A3		REV PER ECR-13-004638	20MAR2013	ML	SZ
		A3		-	-	-	-
		A3		-	-	-	-



- ⚠ DIM S IS CENTERLINE SPACING OF POWER MODULES ON LEFT SIDE OF HOUSING.
- ⚠ DIM T IS CENTERLINE SPACING OF POWER MODULES ON RIGHT SIDE OF HOUSING.
- ⚠ THE MAXIMUM OVERALL LENGTH OF A PART IS 8.00.
- ⚠ PART NUMBER, AND DATE CODE MARKED IN AREA SHOWN. MARKING ON BOTH SIDES PERMITTED FOR PARTS UNDER 2.00 LONG.
- ⚠ MATERIAL:  
HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC, UL94 V-0  
SIGNAL CONTACT - COPPER ALLOY  
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- ⚠ CONTACT PLATING: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA OF POWER AND SIGNAL CONTACTS
- ⚠ MECHANICAL CONNECTOR KEEP OUT ZONE.
- ⚠ DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- ⚠ PCB - ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- ⚠ PCB - .0453±.0010 DRILLED HOLES PLATED WITH .0003 MIN Sn OVER .001 TO .003 Cu PLATING TO ACHIEVE A .040 HOLE.
- ⚠ THE SPECIAL DIMENSION ONLY FOR PART NUMBER 1892130-2 (SEE SHEET 2)



5.100	5.150	.250	.250	2.375	3.250	.450	5.450	8P + 32S + 8P	1892130-4
1.800	1.850	-	-	1.700	.625	.450	2.150	1P + 40S + 1P	1892130-3
7.600	7.650	.200	.200	4.725	4.175	2.025	7.950	64S+11HDP+20S+15HDP	1892130-2
5.100	5.150	.250	.250	3.500	2.175	.450	5.450	7P + 48S + 7P	1892130-1
DIM U	DIM D	DIM T	DIM S	DIM R	DIM W	DIM K	DIM L	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±.01
2 PLC	±.01
3 PLC	±.005
4 PLC	±.0020
ANGLES	±.0020

MATERIAL: 5

FINISH: 6

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: D\_ZHU 16NOV2007

CHK: SUNY\_ZHAO 16NOV2007

APVD: SUNY\_ZHAO 16NOV2007

NAME: RIGHT ANGLE HEADER ASSEMBLY PRESS FIT CONTACT, W/ GUIDES MULTI-BEAM XLE

PRODUCT SPEC: 108-1973

APPLICATION SPEC: 114-13038

SIZE: A1

CAGE CODE: C=1892130

WEIGHT: -

CUSTOMER DRAWING

SCALE: 4:1




SHEET 1 OF 5

REV: A3

LOC	DIST	REV	DATE	BY	APPV
ES	00				

REVISIONS			
NO.	DESCRIPTION	DATE	BY
-	SEE SHEET 1	-	-




PART NUMBER 1892130-2  
 UNSPECIFIED DIMENSION REFER TO SHEET 1

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: D_ZHU 16NOV2007	TE Connectivity NAME: RIGHT ANGLE HEADER ASSEMBLY PRESS FIT CONTACT, W/ GUIDES MULTI-BEAM XLE SIZE: A1 CAGE CODE: 1892130 DRAWING NO: 1892130-2 SCALE: 1:1 SHEET: 2 OF 5 REV: A3
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK: SUNY_ZHAO 16NOV2007	
0 PLC ±. 1 PLC ±.01 2 PLC ±.01 3 PLC ±.005 4 PLC ±0.0020 ANGLES ±.7°	PRODUCT SPEC: 108-1973 APPLICATION SPEC: 114-13038 WEIGHT: -	APVD: SUNY_ZHAO 16NOV2007	
MATERIAL: -	FINISH: -	CUSTOMER DRAWING	



LOC	DIST	REVISIONS			
P	LTN	DESCRIPTION	DATE	DMN	APVD
ES	00	SEE SHEET 1			

PART NUMBER	ROWS	POWER		SIGNAL										POWER		
		PI	P2	1	2	3	4	5	6	7	8	9	10	P1	P2	
1892130-3	D	PM	HD	J	J	J	J	J	J	J	J	J	J	J	PM	HD
	C			K	K	K	F	K	K	K	K	K	K			
	B			N	N	N	N	N	N	N	N	N	N	N		
	A			S	S	S	S	S	S	S	S	S	S	S		
IP + 40S + IP																




THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN: D_ZHU 16NOV2007	TE Connectivity										
DIMENSIONS: INCHES		CHK: SUNY_ZHAO 16NOV2007											
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: SUNY_ZHAO 16NOV2007	NAME: RIGHT ANGLE HEADER ASSEMBLY PRESS FIT CONTACT, W/ GUIDES MULTI-BEAM XLE										
<table border="1"> <tr> <td>0 PLC</td> <td>±</td> </tr> <tr> <td>2 PLC</td> <td>±.10</td> </tr> <tr> <td>3 PLC</td> <td>±.005</td> </tr> <tr> <td>4 PLC</td> <td>±0.0020</td> </tr> <tr> <td>ANGLES</td> <td>±.7°</td> </tr> </table>		0 PLC	±	2 PLC	±.10	3 PLC	±.005	4 PLC	±0.0020	ANGLES	±.7°	PRODUCT SPEC: 108-1973	RESTRICTED TO: A1
0 PLC	±												
2 PLC	±.10												
3 PLC	±.005												
4 PLC	±0.0020												
ANGLES	±.7°												
MATERIAL: -		APPLICATION SPEC: 114-13038	SCALE: 1:1										
FINISH: -		WEIGHT: -	SHEET 4 OF 5										
CUSTOMER DRAWING		REV: -	REV: A3										

LOC	DIST	REVISIONS			
P	LTN	DESCRIPTION	DATE	DMN	APVD
-	-	SEE SHEET 1	-	-	-

PART NUMBER	ROWS	POWER							SIGNAL								POWER							
		P1	P2	P3	P4	P5	P6	P7	P8	1	2	3	4	5	6	7	8	P9	P10	P11	P12	P13	P14	P15
1892130-4	D								Z5	Z5	Z5	Z5	Z5	Z5	Z5	Z5								
	C	TT	TT	TT	TT	TT	TT	TT	Y5	Y5	Y5	Y5	Y5	Y5	Y5	Y5								
	B								R5	R5	R5	R5	R5	R5	R5	R5								
	A	HD							O5	O5	O5	O5	O5	O5	O5	O5								

8P + 32S + 8P



THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN: DENNY ZHU 16NOV2007													
DIMENSIONS: INCHES		CHK: SUNY ZHAO 16MOV2007													
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: SUNY ZHAO 16MOV2007	NAME: RIGHT ANGLE HEADER ASSEMBLY PRESS FIT CONTACT, W/ GUIDES MULTI-BEAM XLE												
<table border="1"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±.01</td></tr> <tr><td>2 PLC</td><td>±.01</td></tr> <tr><td>3 PLC</td><td>±.005</td></tr> <tr><td>4 PLC</td><td>±.0020</td></tr> <tr><td>ANGLES</td><td>±.2°</td></tr> </table>		0 PLC	±	1 PLC	±.01	2 PLC	±.01	3 PLC	±.005	4 PLC	±.0020	ANGLES	±.2°	PRODUCT SPEC: 108-1973	SIZE: A1
0 PLC	±														
1 PLC	±.01														
2 PLC	±.01														
3 PLC	±.005														
4 PLC	±.0020														
ANGLES	±.2°														
MATERIAL: -		APPLICATION SPEC: 114-13038	CAGE CODE: 100779												
FINISH: -		WEIGHT: -	DRAWING NO: 1892130												
CUSTOMER DRAWING		SCALE: 4:1	SHEET 5 OF 5 REV: A3												

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1892130-1](#)