



REVISIONS					
P	LTR	DESCRIPTION	DATE	DMN	APVD
E	REVISED PER	ECO-15-015186	28/MAR/16	PY	YM




1. CHARACTERISTIC IMPEDANCE: 100±10 OHMS (MEASURED DIFFERENTIALLY)

2 LABEL INFORMATION:



3 LABEL INFORMATION:



4. SEE SHEET 2 FOR WIRING SCHEMATIC.

5. ROHS COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE CONNECTIVITY SPECIFICATION TEC-138-702.

24 AWG	15	+0.12 -0	METERS	1-2032757-6
24 AWG	14	+0.12 -0	METERS	1-2032757-5
24 AWG	13	+0.12 -0	METERS	1-2032757-4
24 AWG	12	+0.12 -0	METERS	1-2032757-3
24 AWG	11	+0.12 -0	METERS	1-2032757-2
28 AWG	10	+0.12 -0	METERS	1-2032757-1
28 AWG	9	+0.1 -0	METERS	1-2032757-0
30 AWG	8	+0.1 -0	METERS	2032757-9
30 AWG	7	+0.1 -0	METERS	2032757-8
30 AWG	6	+0.1 -0	METERS	2032757-7
30 AWG	5	+0.1 -0	METERS	2032757-6
30 AWG	4	+0.08 -0	METERS	2032757-5
30 AWG	3	+0.08 -0	METERS	2032757-4
30 AWG	2	+0.08 -0	METERS	2032757-3
30 AWG	1	+0.05 -0	METERS	2032757-2
30 AWG	0.5	+0.05 -0	METERS	2032757-1
CABLE GAUGE		L		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.


DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN	20APR2009	TE Connectivity	
mm		CHK	20APR2009	CABLE ASSY.SFP+ TO SFP+ NI_PLATED	
		APVD	20APR2009	NAME	
				SIZE	CAGE CODE DRAWING NO
				WEIGHT	0
				CUSTOMER DRAWING	SCALE 1:1 SHEET 1 OF 2 REV E

APPROVED: D. LAWRENCE

TE CONNECTIVITY

00779 C=2032757

REVISIONS				
REV	DATE	DESCRIPTION	BY	APP'D
1	-	SEE SHEET 1	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SMITH 20APR2009	
DIMENSIONS: mm		CHK D. LAWRENCE 20APR2009	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		AP'D D. LAWRENCE 20APR2009	NAME CABLE ASSY, SFP+ TO SFP+ NI_PLATED
0. PLC ± - 1. PLC ± - 2. PLC ± - 3. PLC ± - 4. PLC ± - ANGLES ± - FINISH -		PRODUCT SPEC - APPLICATION SPEC -	RESTRICTED TO -
MATERIAL -		WEIGHT -	SIZE A1
CUSTOMER DRAWING		SCALE 1:1	SHEET 2 OF 2
		DRAWING NO. 00779	REV E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2032757-6](#)