



- 1** STAND-OFFS:
 10 THRU 18 POS (2) REQD LOCATED AS SHOWN OUTBIARD OF END CIRCUITS
 20 THRU 38 POS (3) REQD LOCATED OUTBOARD OF END CIRCUITS PLUS (1) CENTERED
 40 THRU 60 POS (4) REQD LOCATED OUTBOARD OF END CIRCUITS WITH (2) EVENLY SPACED WITHIN THE REMAINING LENGTH
- 2** ACCESS SLOT
- 3** OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

| | F | E | D | C | B | A | NO OF POSN | ASSEMBLY PART NUMBER |
|----------|-------|-------|-------|------|-------|----|------------|----------------------|
| OBSOLETE | 3.504 | 3.204 | 2.490 | .190 | 2.800 | 25 | 52 | 2-87813-3 |
| OBSOLETE | 3.404 | 3.104 | 2.390 | .190 | 2.700 | 24 | 50 | 2-87813-2 |
| OBSOLETE | 3.304 | 3.004 | 2.290 | .190 | 2.600 | 23 | 48 | 2-87813-1 |
| OBSOLETE | 3.204 | 2.904 | 2.190 | .190 | 2.500 | 22 | 46 | 2-87813-0 |
| OBSOLETE | 3.104 | 2.804 | 2.090 | .190 | 2.400 | 21 | 44 | 1-87813-9 |
| OBSOLETE | 3.004 | 2.704 | 1.990 | .190 | 2.300 | 20 | 42 | 1-87813-8 |
| OBSOLETE | 2.904 | 2.604 | 1.890 | .190 | 2.200 | 19 | 40 | 1-87813-7 |
| OBSOLETE | 2.804 | 2.504 | 1.790 | .190 | 2.100 | 18 | 38 | 1-87813-6 |
| OBSOLETE | 2.704 | 2.404 | 1.690 | .190 | 2.000 | 17 | 36 | 1-87813-5 |
| | 2.604 | 2.304 | 1.590 | .190 | 1.900 | 16 | 34 | 1-87813-4 |
| OBSOLETE | 2.504 | 2.204 | 1.490 | .190 | 1.800 | 15 | 32 | 1-87813-3 |
| OBSOLETE | 2.404 | 2.104 | 1.390 | .190 | 1.700 | 14 | 30 | 1-87813-2 |
| OBSOLETE | 2.304 | 2.004 | 1.290 | .190 | 1.600 | 13 | 28 | 1-87813-1 |
| OBSOLETE | 2.204 | 1.904 | 1.190 | .190 | 1.500 | 12 | 26 | 1-87813-0 |
| OBSOLETE | 2.104 | 1.804 | 1.090 | .190 | 1.400 | 11 | 24 | 87813-9 |
| OBSOLETE | 2.004 | 1.704 | .990 | .190 | 1.300 | 10 | 22 | 87813-8 |
| OBSOLETE | 1.904 | 1.604 | .890 | .190 | 1.200 | 9 | 20 | 87813-7 |
| OBSOLETE | 1.804 | 1.504 | - | .490 | 1.100 | 8 | 18 | 87813-6 |
| OBSOLETE | 1.704 | 1.404 | - | .390 | 1.000 | 7 | 16 | 87813-5 |
| OBSOLETE | 1.604 | 1.304 | - | .390 | .900 | 6 | 14 | 87813-4 |
| OBSOLETE | 1.504 | 1.204 | - | .290 | .800 | 5 | 12 | 87813-3 |
| OBSOLETE | 1.404 | 1.104 | - | .290 | .700 | 4 | 10 | 87813-2 |
| OBSOLETE | 1.304 | 1.004 | - | .190 | .600 | 3 | 8 | 87813-1 |

THIS DRAWING IS A CONTROLLED DOCUMENT. DIM J GALLUCCI 11OCT89
 DIM R FLICKER 25OCT89

TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0 PLC ± -
 1 PLC ± -
 2 PLC ± -
 3 PLC ± .005
 4 PLC ± -
 ANGLES ± -

FINISH: 50 GOLD IN CONTACT
 COLD FLASH ON SOLDER AREA
 ALL OVER 000050 NICKEL
 ON ENDSIDE POST.

MATERIAL: FLAME RETARDANT THERMOPLASTIC
 HOUSING: COLOR-BLACK
 POST: PHOS. BRONZE

WEIGHT: --
 AREA: --

SIZE: A1
 CASE CODE: --
 DRAWING NO: --

RESTRICTED TO: --

SCALE: 4:1
 SHEET: 1 of 1
 REV: L1

AMP 4805 REV 31MAR2000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-87813-4](#)