




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

| REVISIONS |     |                 |           |     |      |
|-----------|-----|-----------------|-----------|-----|------|
| P         | LTR | DESCRIPTION     | DATE      | DWN | APVD |
|           | A   | INITIAL RELEASE | 30NOV2013 | YC  | BvH  |
|           | A1  | ECR-14-015049   | 13OCT2014 | GSK | BvH  |
|           | A2  | ECR-16-003945   | 16MAR2016 | GSK | BvH  |

NOTES:  
 Tolerances cable lengths:  
 0m to 0.5m +30mm  
 0.5m to 1.0m +50mm  
 1.0m to 3.0m +100mm  
 < 3.0m +1.5%



| TECHNICAL DATA                |   |
|-------------------------------|---|
| Operating voltage             | 24 V DC ±25 %   |
| Operating current per contact | max. 4 A  |
| Locking of ports              | Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing |
| Protection                    | IP65 and IP67 when plugged and screwed down (EN 60529)            |

| PUR/PVC CABLE              |                          |
|----------------------------|--------------------------|
| No./diameter of wires      | 4 x 0.34 mm <sup>2</sup> |
| Wire isolation             | PVC (br, wh, bl, bk)     |
| C-track properties         | 2 million                |
| Jacket                     | PUR/PVC                  |
| Outer diameter             | approx. 5.2 mm           |
| Bend radius (moving)       | 15 x outer diameter      |
| Temperature range (fixed)  | -30...+80 °C             |
| Temperature range (mobile) | -5...+80 °C              |

| CABLE                      |                                  |
|----------------------------|----------------------------------|
| No./diameter of wires      | 4 x 0.34 mm <sup>2</sup>         |
| Wire isolation             | PP (br, wh, bl, bk)              |
| C-track properties         | 10 million                       |
| Jacket                     | PUR (UL/CSA), welding spark res. |
| Outer diameter             | approx. 4.7 mm                   |
| Bend radius (moving)       | 10 x outer diameter              |
| Temperature range (fixed)  | -40...+90 °C                     |
| Temperature range (mobile) | -25...+90 °C                     |

| POS   | LENGTH "L" | MATERIAL        | JACKET COLOR | TE PN       | DESCRIPTION            | ITEM |
|-------|------------|-----------------|--------------|-------------|------------------------|------|
| 4 pos | 2.0mtr     | SPARK RESISTANT | Black        | 3-2273126-5 | 4x22AWG SPARK RES 2.0m | 20   |
|       | 1.5mtr     |                 |              | 3-2273126-4 | 4x22AWG SPARK RES 1.5m | 19   |
|       | 1.0mtr     |                 |              | 3-2273126-3 | 4x22AWG SPARK RES 1.0m | 18   |
|       | 0.6mtr     |                 |              | 3-2273126-2 | 4x22AWG SPARK RES 0.6m | 17   |
|       | 0.3mtr     |                 |              | 3-2273126-1 | 4x22AWG SPARK RES 0.3m | 16   |
| 4 pos | 2.0mtr     | PUR/PVC         | Black        | 2-2273126-5 | 4x22AWG PUR/PVC 2.0m   | 15   |
|       | 1.5mtr     |                 |              | 2-2273126-4 | 4x22AWG PUR/PVC 1.5m   | 14   |
|       | 1.0mtr     |                 |              | 2-2273126-3 | 4x22AWG PUR/PVC 1.0m   | 13   |
|       | 0.6mtr     |                 |              | 2-2273126-2 | 4x22AWG PUR/PVC 0.6m   | 12   |
|       | 0.3mtr     |                 |              | 2-2273126-1 | 4x22AWG PUR/PVC 0.3m   | 11   |

| TECHNICAL DATA                |   |
|-------------------------------|---|
| Operating voltage             | 24 V DC ±25 %   |
| Operating current per contact | max. 4 A  |
| Locking of ports              | Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing |
| Protection                    | IP65 and IP67 when plugged and screwed down (EN 60529)            |

| PUR CABLE                  |                          |
|----------------------------|--------------------------|
| No./diameter of wires      | 4 x 0.34 mm <sup>2</sup> |
| Wire isolation             | PP (br, wh, bl, bk)      |
| C-track properties         | 5 million                |
| Jacket                     | PUR (UL/CSA)             |
| Outer diameter             | approx. 4.7 mm           |
| Bend radius (moving)       | 10 x outer diameter      |
| Temperature range (fixed)  | -40...+80 °C             |
| Temperature range (mobile) | -25...+80 °C             |

| PVC CABLE                  |                          |
|----------------------------|--------------------------|
| No./diameter of wires      | 4 x 0.34 mm <sup>2</sup> |
| Wire isolation             | PVC (br, wh, bl, bk)     |
| C-track properties         |                          |
| Jacket                     | PVC (UL/CSA)             |
| Outer diameter             | approx. 5.0 mm           |
| Bend radius (moving)       | 10 x outer diameter      |
| Temperature range (fixed)  | -30...+80 °C             |
| Temperature range (mobile) | -5...+80 °C              |

| POS   | LENGTH "L" | MATERIAL | JACKET COLOR | TE PN       | DESCRIPTION      | ITEM |
|-------|------------|----------|--------------|-------------|------------------|------|
| 4 pos | 2.0mtr     | PVC      | Black        | 1-2273126-5 | 4x22AWG PVC 2.0m | 10   |
|       | 1.5mtr     |          |              | 1-2273126-4 | 4x22AWG PVC 1.5m | 9    |
|       | 1.0mtr     |          |              | 1-2273126-3 | 4x22AWG PVC 1.0m | 8    |
|       | 0.6mtr     |          |              | 1-2273126-2 | 4x22AWG PVC 0.6m | 7    |
|       | 0.3mtr     |          |              | 1-2273126-1 | 4x22AWG PVC 0.3m | 6    |
| 4 pos | 2.0mtr     | PUR      | Black        | 2273126-5   | 4x22AWG PUR 2.0m | 5    |
|       | 1.5mtr     |          |              | 2273126-4   | 4x22AWG PUR 1.5m | 4    |
|       | 1.0mtr     |          |              | 2273126-3   | 4x22AWG PUR 1.0m | 3    |
|       | 0.6mtr     |          |              | 2273126-2   | 4x22AWG PUR 0.6m | 2    |
|       | 0.3mtr     |          |              | 2273126-1   | 4x22AWG PUR 0.3m | 1    |

THIS DRAWING IS A CONTROLLED DOCUMENT. DWN YATHISH.C 30NOV2013  
 CHK B.VELDHoven 30NOV2013  
 APVD A.VAN ZANDVOORT 30NOV2013  
 PRODUCT SPEC 108-19483  
 APPLICATION SPEC 114-32127

**TE** TE Connectivity  
 M12 ANGLD SCKT TO M12 STRGHT PLG 3 LED

SIZE A2 CAGE CODE 00779 DRAWING NO. C=2273126 RESTRICTED TO -  
 SCALE NTS SHEET 1 OF 1 REV A2

CUSTOMER DRAWING

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2273126-4](#)