





LOC		DIST		REVISIONS			
CM	00	REV	DESCRIPTION	DATE	DMN	APVD	
		G2	REVISED PER ECO-08-019746	13AUG08	HMR	DC	
		G3	REV PER ECO-09-021826	08SEP09	KK	AEG	



- 1 MATES WITH AMP CONNECTOR PART NO 480704.
- $\Delta 2$ FLAME RETARDANT CLASSIFICATION OF MATERIAL IS 94V-2.
- 3 PARTS MUST COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
- $\Delta 4$ CONTACT IS STAMPED FROM PRE-PLATED STOCK WHICH IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN STRIPED WITH 0.00076 [.000030] GOLD IN CONTACT AREA INDICATED AND TIN-LEAD ON SOLDER TAIL END.
- $\Delta 5$ CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- $\Delta 6$ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED LAYOUT FOR 3.18 [.125] THICK PC BOARD

$\Delta 6$ OBSOLETE	PH BRZ GOLD $\Delta 5$	NYLON, NATURAL $\Delta 2$	350989-5
	PH BRZ TIN	NYLON, NATURAL $\Delta 2$	350989-4
	PH BRZ GOLD $\Delta 4$	NYLON, NATURAL $\Delta 2$	350989-3
	CONTACT	HOUSING	PART NO

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN K. WHITAKER 11OCT2005	11OCT2005	Tyco Electronics Corporation Harrisburg, PA 17105-3608
0. PLC ±	1. PLC ±	CHK S. RIDGILL 11OCT2005	11OCT2005	APVD S. RIDGILL 11OCT2005
2. PLC ±	3. PLC ±	NAME	NAME	NAME
4. PLC ±	ANGLES ±	APPLICATION SPEC	APPLICATION SPEC	APPLICATION SPEC
FINISH	FINISH	WEIGHT	WEIGHT	WEIGHT
SEE TABLE	SEE TABLE	WEIGHT	WEIGHT	WEIGHT

SOCKET HEADER ASSEMBLY, 6 CIRCUIT, LONG TAIL, UNIVERSAL MATE-N-LOK (TM)

SIZE: A1 CAGE CODE: 00779 DRAWING NO: 350989

CUSTOMER DRAWING SCALE: 5:1 SHEET: 1 OF 1 REV: G3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[350989-4](#)