

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
IN	00		A1	ECO-14-002553	21FEB2014	KP	LV

ISOMETRIC VIEW

1 SHELL: ZINC.
OUTER CONTACT: COPPER.
RETAINING RING: BRASS.
DIELECTRIC: POLYESTER PBT, NATURAL.


2 SHELL: 2.0 μ m MIN TIN OVER 1.0 μ m MIN NICKEL, BOTH OVER 5.08 μ m MIN COPPER.
OUTER CONTACT: 3.75 μ m MIN TIN OVER 1.27 μ m MIN NICKEL.
RETAINING RING: 2.03 μ m MIN TIN OVER 1.27 μ m MIN NICKEL.

3 PLUG SUBASSEMBLY ACCEPTS JACK SUBASSEMBLIES MEETING DIN 72594-1, ROAD VEHICLES - RADIO FREQUENCY INTERFACE - DIMENSIONS AND ELECTRICAL REQUIREMENTS.

4. SEE INSTRUCTION SHEET 408-10028.

1924937-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. PETERSON 13FEB2012	 TE Connectivity		
DIMENSIONS: mm		CHK L. VARSIK 13FEB2012			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD L. VARSIK 13FEB2012	NAME PLUG SUBASSEMBLY, RG-316 OR RG-174, SMB		
0 PLC \pm - 1 PLC \pm - 2 PLC \pm - 3 PLC \pm - 4 PLC \pm - ANGLES \pm -		PRODUCT SPEC -	RESTRICTED TO -		
MATERIAL - 1		APPLICATION SPEC 114-13157	SIZE A3	CAGE CODE 00779	DRAWING NO 1924937
FINISH - 2		WEIGHT -	SCALE 5:1		
		CUSTOMER DRAWING		SHEET 1 OF 1 REV A1	

1470-19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1924937-1](#)