






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	ECN	DATE	APVD
	B	REVISED	ECR-15-007169	30OCT2015	K.K E.T



900121-2  
 (A1) 5900121-2  
 SMALL

900121-4  
 (A1) 5900121-4  
 LARGE

LARGE	3	1	STEEL	t=0.9	5900121-4	(A1)
SMALL	3	1	STEEL	t=0.9	5900121-2	(A1)
LARGE	2	1	STEEL	t=0.9	900121-4	
<del>SMALL</del>	<del>2</del>	<del>1</del>	<del>STEEL</del>	<del>t=0.9</del>	<del>900121-2</del>	
NAME	FINISH	MATERIAL	PART NO.			

OBSOLETE

- △ MATERIAL : CARBON STEEL, THICKNESS=0.9±0.1mm
- △ FINISH : CHROMATE (Zn PLATE)
- (A1) △ FINISH : AFTER Cu GROUND PLATING 2.5μmMIN OF ALL ASPECTS, Ni PLATE 2.5μmMIN
- △ 材料 : スチール 板厚=0.9±0.1mm
- △ 仕上 : クロメート(亜鉛めっき)処理
- (A1) △ 仕上 : 全面銅下地めっき2.5μm以上の上に, Niめっき2.5μm以上を施す

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	M. MAEBASHI	05DEC2005	 TE Connectivity			
CHK	T. SAKAMOTO	06JAN2006				
APVD	D. MITSUGI	10JAN2006				
NAME	L METAL HOOK FOR DYNAMIC FREE HANGING (D-3)					
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
単位: 概 mm	一般公差 ±0.3, ±3°	108-5349	A3	00779	C-900121	-
	0 PLC ±	APPLICATION SPEC	SCALE	SHEET	OF	REV
	1 PLC ±0.5	取付適用規格	尺度	3:1	1	B
	2 PLC ±0.13	WEIGHT	Customer Drawing			
	3 PLC ±0.013					
	4 PLC ±0.0001					
	ANGLES ±					
MATERIAL	FINISH					
材料	仕上					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5900121-4](#)