





LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
-	-	B		REV PER ECO 12-010940	7-31-12	CT	DH	
		C		ECO-13-004755	26MAR2013	KG	DH	
		D		ECO-14-017030	23NOV2014	CT	MGM	



- 1 MATERIAL:
CONTACT AND SHIELD: COPPER ALLOY
HOUSING AND CHICKLET: LCP, COLOR: BLACK
- 2 FINISH:
CONTACT: MATING AREA: 1.27µm MIN GOLD OVER
1.27µm MIN NICKEL
SHIELD: 1.27µm MIN NICKEL
- 3 FINISH:
COMPLIANT PIN AREA: 0.38µm MIN BRIGHT TIN LEAD OVER
1.27µm MIN NICKEL
- 4 FINISH:
COMPLIANT PIN AREA: 0.38µm MIN MATTE TIN OVER
1.27µm MIN NICKEL
- 5 ---
- 6 DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- 7 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 8 REFERENCE APPLICATION SPEC 114-13267 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 9 ALL GROUNDS IN ODD NUMBERED COLUMNS ARE COMMONED.
ALL GROUNDS IN EVEN NUMBERED COLUMNS, EXCEPT FOR ROW A
ARE COMMONED.



2 4	2000892-2
2 3	2000892-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (150 STANDARDS)		DWN D. BELACK 24JUN2009	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK A. TSANG 6-24-2009	NAME Fortis Zd. 3-PAIR, 10-COLUMN, RIGHT ANGLE, RIGHT MODULE ASSEMBLY, DIFFERENTIAL PAIR	
DIMENSIONS:		APVD W. McALONIS 6-24-2009	SIZE CAGE CODE DRAWING NO	
mm		PRODUCT SPEC 108-2409	RESTRICTED TO	
0 PLC ±.13		APPLICATION SPEC 114-13267	A100779C=2000892	
1 PLC ±0.05		WEIGHT ~13.47g	Customer Drawing	
2 PLC ±.13		SCALE 5:1	SHEET 1 OF 1	
3 PLC ±.13		REV D		
4 PLC ±.13				
ANGLES ±.2°				
FINISH				
-				
-				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2000892-2](#)