




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
FT	0		G2	REVISED PER ECO-13-014760		19SEP13	MM

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-0, BLACK.
TERMINALS: BRIGHT TIN OVER COPPER ALLOY.
SCREWS: #6-32 STEEL, ZINC PLATING W/ CLEAR CHROMATE,
EXCEPT WHERE NOTED OTHERWISE.

ELECTRICAL:
RATED CURRENT UL/CSA:
CLASS C: 20A, 300V.
CLASS D: 5A, 600V.
WIRE RANGE: 12-22 AWG

MECHANICAL:
RECOMMENDED TORQUE: 7 IN-LB.
OPERATING TEMP.: 105°C MAX.

- 1 SCREWS BOTTOMED.
- 2 NO SCREWS.
- 3 SCREWS ARE NICKEL PLATED BRASS.
- 4 PRELIMINARY





RECOMMENDED PCB LAYOUT

7.186	19	JC6-P108-19	4-796985-6
6.811	18	JC6-P108-18	4-796985-5
6.436	17	JC6-P108-17	5-1437666-7
6.061	16	JC6-P108-16	3-1437665-2
5.686	15	JC6-P108-15	4-796985-4
5.311	14	JC6-P108-14	3-1437665-1
4.936	13	JC6-P108-13	4-796985-3
4.561	12	JC6-P106-12	1776249-8
4.561	12	JC6-P108-12	3-1437665-0
4.186	11	JC6-P108-11-170	1-796985-5
4.186	11	JC6-P108-11	2-1437665-9
3.811	10	JC6-P108-10	2-1437665-8
3.436	9	JC6-P106-09	1776249-7
3.436	9	JC6-P108-09	796985-3
3.061	8	JC6-P106-08	1776249-3
3.061	8	JC6-P108-08	2-1437665-7
2.686	7	JC6-P106-07	1776249-2
2.686	7	JC6-P108-07	4-796985-2
2.311	6	JC6-P106-06	1776249-6
2.311	6	JC6-P108-06-169	1-796985-4
2.311	6	JC6-P108-06	2-1437665-5
1.936	5	JC6-P106-05	1776249-1
1.936	5	JC6-P108-05-161	2-1437665-4
1.936	5	JC6-P108-05	2-1437665-3
1.561	4	JC6-P108-04-230	1-1776249-0
1.561	4	JC6-P106-04	1776249-5
1.561	4	JC6-P108-04-186	796985-8
1.561	4	JC6-P108-04-167	1-796985-2
1.561	4	JC6-P108-04	2-1437665-2
1.186	3	JC6-P108-03-229	1776249-9
1.186	3	JC6-P106-03	1776249-4
1.186	3	JC6-P108-03	2-1437665-1
.811	2	JC6-P108-02-161	1-1776249-1
.811	2	JC6-P108-02	2-1437665-0
DIM. "A"	NO. OF POS.	CATALOG PART NO.	PART NO.

SEE FIGURE

SEE FIGURE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 18JUN02		<div>TE Connectivity</div>											
		CHK S. YODER 6/18/02													
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME											
		APVD S. YODER 6/18/02		JC6-P108-106-XX ASSEMBLY											
		PRODUCT SPEC —													
		APPLICATION SPEC —													
		WEIGHT —													
0 PLC ± — 1 PLC ± — 2 PLC ± .01 3 PLC ± .005 4 PLC ± — ANGLES ± —		SIZE A3		CAGE CODE 00779		DRAWING NO C-2-1437665-0		RESTRICTED TO —							
MATERIAL —		FINISH —		CUSTOMER DRAWING						SCALE NTS		SHEET 1 OF 2		REV G2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-796985-2](#)