




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	L	RESIN SUPPLIER CHANGE FOR THE HOUSING	15DEC2021	SCB	KJK





NOTES:

- 1 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3 MATERIAL: HOUSING— FLAME RETARDANT THERMOPLASTIC, COLOR—BLACK
POSTS— COPPER ALLOY
- 4 FINISH: POSTS— .000030 GOLD ON CONTACT AREA,
.000100—.000200 MATTE TIN—LEAD ON SOLDERTAIL,
ALL OVER .000050 NICKEL
- 5 FINISH: POSTS— .000030 GOLD ON CONTACT AREA,
.000100—.000200 MATTE TIN ON SOLDERTAIL,
ALL OVER .000050 NICKEL
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI





SECTION X-X



RECOMMENDED HOLE LAYOUT

6	OBSOLETE	5	2.806	.106	3.032	2.900	29	60	7-102699-8	
		5	2.306	.106	2.532	2.400	24	50	7-102699-3	
		5	1.806	.106	2.032	1.900	19	40	6-102699-9	
		5	1.506	.106	1.732	1.600	16	34	6-102699-6	
		5	1.306	.106	1.532	1.400	14	30	6-102699-4	
		5	1.106	.106	1.332	1.200	12	26	6-102699-2	
		5	1.006	.106	1.232	1.100	10	24	6-102699-1	
		5	.806	.106	1.032	.900	9	20	5-102699-9	
		5	—	.406	.932	.800	8	18	5-102699-8	
		5	—	.306	.832	.700	7	16	5-102699-7	
		5	—	.306	.732	.600	6	14	5-102699-6	
		5	—	.206	.632	.500	5	12	5-102699-5	
		5	—	.206	.532	.400	4	10	5-102699-4	
6	OBSOLETE	5	—	.106	.432	.300	3	8	5-102699-3	
		5	—	.106	.332	.200	2	6	5-102699-2	
		4	2.806	.106	3.032	2.900	29	60	2-102699-8	
		OBSOLETE	4	2.706	.106	2.932	2.800	28	58	2-102699-7
		OBSOLETE	4	2.606	.106	2.832	2.700	27	56	2-102699-6
		OBSOLETE	4	2.506	.106	2.732	2.600	26	54	2-102699-5
		OBSOLETE	4	2.406	.106	2.632	2.500	25	52	2-102699-4
			4	2.306	.106	2.532	2.400	24	50	2-102699-3
			4	2.206	.106	2.432	2.300	23	48	2-102699-2
		OBSOLETE	4	2.106	.106	2.332	2.200	22	46	2-102699-1
		OBSOLETE	4	1.906	.106	2.132	2.000	20	42	2-102699-0
			4	1.806	.106	2.032	1.900	19	40	1-102699-9
			4	1.706	.106	1.932	1.800	18	38	1-102699-8
BY 6-102699-6	OBSOLETE	4	1.606	.106	1.832	1.700	17	36	1-102699-7	
			4	1.506	.106	1.732	1.600	16	34	1-102699-6
			4	1.406	.106	1.632	1.500	15	32	1-102699-5
			4	1.306	.106	1.532	1.400	14	30	1-102699-4
		OBSOLETE	4	1.206	.106	1.432	1.300	13	28	1-102699-3
			4	1.106	.106	1.332	1.200	12	26	1-102699-2
			4	1.006	.106	1.232	1.100	11	24	1-102699-1
		OBSOLETE	4	.906	.106	1.132	1.000	10	22	1-102699-0
			4	.806	.106	1.032	.900	9	20	102699-9
			4	—	.406	.932	.800	8	18	102699-8
			4	—	.306	.832	.700	7	16	102699-7
			4	—	.306	.732	.600	6	14	102699-6
			4	—	.206	.632	.500	5	12	102699-5
	4	—	.206	.532	.400	4	10	102699-4		
	4	—	.106	.432	.300	3	8	102699-3		
	4	—	.106	.332	.200	2	6	102699-2		
	OBSOLETE	4	2.006	.106	2.232	2.100	21	44	102699-1	

FINISH		E	D	C	B	A	NO OF POSN		ASSEMBLY PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R BROWN 14APROS		<div>TE Connectivity</div>					
DIMENSIONS: INCHES		CHK R BROWN 14APROS								
		APVD J GEFORD 14APROS		NAME HDR ASSY, MOD II, COMPLIANT PIN, DBL ROW, .100x.100 CL, 4 SIDE SHROUD						
		PRODUCT SPEC								
		APPLICATION SPEC								
		WEIGHT —								
		CUSTOMER DRAWING								
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE CAGE CODE DRAWING NO		RESTRICTED TO						
0 PLC ± —		A1 00779 102699		—						
1 PLC ± —										
2 PLC ± —										
3 PLC ± .005										
4 PLC ± —										
ANGLES ± —										
MATERIAL —		FINISH SEE TABLE		SCALE 4:1 SHEET 1 of 1 REV L						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[102699-5](#)