


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

- 1 HOUSING: FLAME RETARDANT, GLASS FILLED, POLYESTER, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE
VACUUM COVER: STAINLESS STEEL
- 2 CONTACT: DUPLEX PLATED 0.76µm[.000030] GOLD IN CONTACT AREA, 3.81-7.62µm[.000150-.000300] BRIGHT TIN-LEAD ON, LEADS, ALL OVER 1.27µm[.000050] MINIMUM NICKEL
- 3 THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY NOT TO CONTACT LOCATIONS
- 4 MARK PART NUMBER AND DATE CODE, IN APPROXIMATE LOCATION SHOWN, EITHER SIDE.
- 5 TOLERANCE IS NON-CUMULATIVE.
- 6 2 POSITION DATE CODE IS MARKED OPPOSITE SIDE OF TE CONNECTIVITY LOGO.
- 7 POINT OF MEASUREMENT DIMENSION FOR PLATING THICKNESS (INSIDE CONTACT BEAM).
- 8 POINT-OF-CONTACT DIMENSION.
- 9 ø5.51[.217] MIN TARGET AREA FOR VACUUM PICK UP. COVER TO BE REMOVED AFTER SOLDERING.
- 10 PACKAGED IN TAPE & REEL PER EIA 481 SPECIFICATION.
- 11 TE CONNECTIVITY TRADEMARK AND CSA LOGO ARE MOLDED INTO HOUSING.
- 12 NO PART NUMBER REQUIRED ON THIS PART.
- 13 CONTACT: DUPLEX PLATE CONNECTIVITYD 0.76µm[.000030] GOLD IN CONTACT AREA, 3.81-7.62µm[.000150-.000300] MATTE TIN ON LEADS, ALL OVER 1.27µm[.000050] MINIMUM NICKEL.
- 14 ROHS 2002/95/EC COMPLIANT.
- 15 SUPERRSEDED BY 6-147105-5
- 16 SUPERRSEDED BY 6-147105-8
- 17 SUPERRSEDED BY 7-147105-2
- 18 SUPERRSEDED BY 8-147105-0

120mm	99.06[3.900]	101.60[4.000]	80	9-147105-0	
	96.52[3.800]	99.06[3.900]	78	8-147105-9	
	93.98[3.700]	96.52[3.800]	76	8-147105-8	
	91.44[3.600]	93.98[3.700]	74	8-147105-7	
	88.90[3.500]	91.44[3.600]	72	8-147105-6	
	86.36[3.400]	88.90[3.500]	70	8-147105-5	
	83.82[3.300]	86.36[3.400]	68	8-147105-4	
	81.28[3.200]	83.82[3.300]	66	8-147105-3	
	78.74[3.100]	81.28[3.200]	64	8-147105-2	
	76.20[3.000]	78.74[3.100]	62	8-147105-1	
	73.66[2.900]	76.20[3.000]	60	8-147105-0	
	71.12[2.800]	73.66[2.900]	58	7-147105-9	
88mm	68.58[2.700]	71.12[2.800]	56	7-147105-8	
	66.04[2.600]	68.58[2.700]	54	7-147105-7	
	63.50[2.500]	66.04[2.600]	52	7-147105-6	
	60.96[2.400]	63.50[2.500]	50	7-147105-5	
	58.42[2.300]	60.96[2.400]	48	7-147105-4	
72mm	55.88[2.200]	58.42[2.300]	46	7-147105-3	
	53.34[2.100]	55.88[2.200]	44	7-147105-2	
	50.80[2.000]	53.34[2.100]	42	7-147105-1	
	48.26[1.900]	50.80[2.000]	40	7-147105-0	
	45.72[1.800]	48.26[1.900]	38	6-147105-9	
	43.18[1.700]	45.72[1.800]	36	6-147105-8	
	40.64[1.600]	43.18[1.700]	34	6-147105-7	
	38.10[1.500]	40.64[1.600]	32	6-147105-6	
	35.56[1.400]	38.10[1.500]	30	6-147105-5	
	33.02[1.300]	35.56[1.400]	28	6-147105-4	
44mm	30.48[1.200]	33.02[1.300]	26	6-147105-3	
	27.94[1.100]	30.48[1.200]	24	6-147105-2	
	25.40[1.000]	27.94[1.100]	22	6-147105-1	
	22.86[.900]	25.40[1.000]	20	6-147105-0	
	20.32[.800]	22.86[.900]	18	5-147105-9	
	17.78[.700]	20.32[.800]	16	5-147105-8	
	15.24[.600]	17.78[.700]	14	5-147105-7	
	12.70[.500]	15.24[.600]	12	5-147105-6	
	10.16[.400]	12.70[.500]	10	5-147105-5	
	7.62[.300]	10.16[.400]	8	5-147105-4	
24mm	5.08[.200]	7.62[.300]	6	5-147105-3	
	2.54[.100]	5.08[.200]	4	5-147105-2	
12	6	2	5-147105-1		
FINISH	EIA TAPE WIDTH	B	A	NO.OF POSN.	PART NUMBER

12 6 OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV02	 TE Connectivity Ltd.		
DIMENSIONS: mm [INCHES]		CHK J.OLSON 06NOV02			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.OLSON 06NOV02	NAME RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, SURFACE MOUNT, AMPMODU		
0 PLC ± - 1 PLC ± - 2 PLC ± .005[0.13] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-25022	SIZE A2	CAGE CODE 00779	DRAWING NO C=147105
MATERIAL 1		FINISH SEE TABLE	WEIGHT -	RESTRICTED TO -	
CUSTOMER DRAWING			SCALE 1:1	SHEET 2 OF 2	REV K

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-147105-2](#)