









4-25018	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-	A1	00779	C=147747	-
OWNER DRAWING			SCALE 6:1	SHEET 1 OF 2 REV J





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. NO. M-BINNER 20MAY02 CHK. J. OLSON 20MAY02 APP'D. J. OLSON 20MAY02		 TE Connectivity Ltd.	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 P/LC ± - 1 P/LC ± - 2 P/LC ± - 3 P/LC ± 0.005[-.13] 4 P/LC ± 0.0005[0.13] ANGLES ± - FINISH		NAME RCPT ASSY, MOD IV, DOUBLE ROW, VERTICAL, DUAL ENTRY, .100X.100 C/L, SURFACE MOUNT, AMPMODU	
		PRODUCT SPEC. 103-25022		SIZE A1	
MATERIAL 		APPLICATION SPEC. 114-25018		GAGE CODE 00779	
		WEIGHT -		DRAWING NO. 147747	
				RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE: 6:1 SHEET 1 OF 2 REV. J	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—





UNREELING DIRECTION

VIEW Y



- 1 HOUSING: GLASS FILLED, FLAME RETARDANT POLYESTER, BLACK CONTACTS: PHOSPHOR BRONZE.
VACUUM COVER: STAINLESS STEEL
- 2 CONTACTS: DUPLEX PLATED—0.76 μ m [.000030] GOLD IN CONTACT AREA, 3.81—7.62 μ m [.000150—.000300] BRIGHT TIN—LEAD ON, LEADS, ALL OVER 1.27 μ m [.000050] MIN NICKEL.
- 3 DIMENSION APPLIES TO HOUSING CAVITY CENTERLINES ONLY.
- 4 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 5 POINT OF CONTACT DIMENSION.
- 6 MARK PART NUMBER AND DATE CODE IN APPROXIMATE LOCATION SHOWN, EITHER SIDE.
- 7 TOLERANCE IS NON—CUMULATIVE.
- 8 5.5 [.217] MIN TARGET AREA FOR VACUUM PICK—UP COVERS TO BE REMOVED AFTER SOLDERING.
- 9 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 10 NO CENTER HOLD DOWNS
- 11 PACKAGED IN TAPES AND REEL PER EIA 481 SPECIFICATIONS.
- 12 FOR 2 POS, DATE CODE IS STAMPED OPPOSITE SIDE OF TE LOGO.
- 13 TE TRADEMARK AND CSA LOGO ARE MOLDED INTO HOUSING.
- 14 NO PART NUMBER MARKING REQUIRED ON THIS PART.
- 15 CONTACTS: DUPLEX PLATED—0.76 μ m [.000030] GOLD IN CONTACT AREA, 3.81—7.62 μ m [.000150—.000300] MATTE TIN ON LEADS, ALL OVER 1.27 μ m [.000050] MIN NICKEL.
- 16 ROHS 2002/95/EC COMPLIANT

[illegible]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. NO.	M-BINNER		20MAY02	 TE Connectivity Ltd.	
		CHK.	J. OLSON		20MAY02		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		J. OLSON	20MAY02	NAME	RCPT ASSY, MOD IV, DOUBLE ROW, VERTICAL, DUAL ENTRY, .100X.100 C/L, SURFACE MOUNT, AMPMODU
mm (INCHES)		0 P/LC ± - 1 P/LC ± - 2 P/LC ± - 3 P/LC ± 0.005 (0.13) 4 P/LC ± 0.0005 (0.13) ANGLES ± -		PRODUCT SPEC			
		FINISH		APPLICATION SPEC			
MATERIAL		WEIGHT		SIZE			
		-		CAGE CODE		DRAWING NO.	RESTRICTED TO
		-		A1		00779	147747
		CUSTOMER DRAWING		SCALE		SHEET	REV
				1:1		2 OF 2	J

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-147747-5](#)