





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL CREATED	15MAY2022	CL	WH



- NOTES:
- MATERIAL AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702
 - MATERIAL CHARACTER
2.92 CONNECOTR:
BODY & NUT: STAINLESS STEEL
CONTACT: BeCU GOLD PLATING
INSULATION: PEI
CABLE: HI-FLEXIBLE,BLUE
 - PRODUCT RATING:
TEMPERATURE: -40°C TO +85°C
VOLTAGE: 250V (RMS)
CHARACTERISTIC IMPEDANCE: 50 OHMS Normal
FREQUENCY RANGE: DC TO 40GHz
DURABILITY: NO LESS THAN 500TIMES
CABLE RETENTION FORCE: 110N MIN
BEND RADIUS: 14MM MIN (STATIC)
35MM MIN(REPEATED)
 - CABLE ASSEMBLY TO BE 100% SI TESTED
VSWR: 1.40:1 MAX @ DC~40GHz
INSERT LOSS: REFER TO TABLE
 - 2.92 CONNECTOR COUPLING TORUE: 0.9±0.1Nm
 - CONNECTOR NEED COVER WITH CAP,PACKAGE FOLLOW TEC-107-115
 - MATE WITH 2081408-1(NEED SEPARATE TO BUY)

1-2016742-0	39.4±0.30INCH	1000±15MM	-7.10dB MIN@40GHz
20166742-9	36.0±0.30INCH	910±15MM	-6.60dB MIN@40GHz
20166742-6	24.0±0.25INCH	610±12MM	-4.80dB MIN@40GHz
20166742-3	12.0±0.20INCH	305±9MM	-3.20dB MIN@40GHz
20166742-1	6.0±0.10ICH	153±6MM	-1.70dB MIN@40GHz
TE PN		LENGTH	INSERTION LOSS

2	PC	SCREW	3
1	PC	SHELL	2
8	PC	SMPM TO 2.92,M-M,BLUE CABLE,40GHz	1
Q'TY	UNIT	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 21APR2022 Cedar Liu	 TE Connectivity	
		CHK 07MAY2022 Cedar Liu		
DIMENSIONS: mm		APVD - Wenke He	NAME MULTI-PORT CA,8 IN 1,SMPM TO 292 UP TO 40GHz	
		PRODUCT SPEC -		
		APPLICATION SPEC -	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL TBD		WEIGHT -	A3 00779 C-2016742	
		FINISH - finish_spec_2	SCALE 1:2 SHEET 1 OF 1 REV A	
		CUSTOMER DRAWING		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2016742-6](#)