



The 5 GHz omnidirectional antenna systems offered by Laird are constructed of UV-stable fiberglass with all stainless-steel brackets standard. They have type N female bulkhead connectors. N male connectors also available for mounting directly to equipment. The horizontal pattern is a full 360 degrees with gain flatness better than 2 dB. The antennas are vented at the base to prevent any moisture build-up inside. Antennas are DC grounded for lightning protection.

FEATURES AND BENEFITS

- 12 dBi antenna gain
- Type N female integrated bulkhead connector
- Rugged, lightweight, and waterproof
- Also available with N male connector
- All stainless-steel bracket for better corrosion protection
- Extra wide strap and larger diameter base for better stability
- Extended connector shroud and extended length N connector for easier/more reliable weatherproofing

APPLICATIONS

- 5.4 to 5.8 GHz ISM band applications
- Base station antennas
- 802.11a wireless systems
- Point-to-multi-point systems
- Wireless broadband systems
- WLAN access points
- Mesh networks
- WiMax

ELECTRICAL SPECIFICATIONS

Operating Frequency (MHz)	5470-5850
VSWR	1.5:1
Gain (dBi)	12
Nominal Impedance (Ohms)	50
Max Power - Ambient 25°C (W)	100
Vertical Plane 3 dB Beamwidth	7°
Horizontal Plane 3dB Beamwidth	360°

MECHANICAL SPECIFICATIONS

Pole Diameter (OD) – mm (in.)	25.0-51.0 (1.0-2.0)
Dimensions – diameter x height – mm (inches)	20 x 25-51 (0.8 x 1-2)
Weight – kg (lbs.)	0.5 (1.1)
Lightning Protection	DC Grounded

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature – °C (°F)	-40 to +70°C (-40 to +158°F)
Wind Velocity – m/sec (mph)	56 (125)
Wind Loading – km/hr (mph)	8.75lb @ 160.9 (100), 13.7lb @ 201 (125)
Material Substance Compliance	RoHs compliant

CONFIGURATION


PART NUMBER	DESCRIPTION
OD58-12	12 dBi 5740-5850 MHz wide-band omnidirectional antenna
OD58M-12	12 dBi 5740-5850 MHz wide-band omnidirectional antenna with N-male connector

MOUNTING OPTIONS



Figure 1: Mast Mount

RADIATION PATTERNS



Americas: +1.847.839.6925
 IAS-AmericasSales@lairdtech.com
Europe: +44.1628.858941
 IAS-EUSales@lairdtech.com
Asia: IAS-AsiaSales@lairdtech.com
Middle East and Africa: +44.1628.858941
 IAS-MEASales@lairdtech.com
www.lairdtech.com

✓RoHS

Laird warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations Laird will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the Laird product is installed. Useful lifetime of the original end product may vary but is not to exceed five (5) years from the original date of the end product purchase.

Any information furnished by Laird Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird materials rests with the end user, since Laird and its agents cannot be aware of all potential uses. Laird makes no warranties as to the fitness, merchantability or suitability of any Laird materials or products for any specific or general uses. Laird shall not be liable for incidental or consequential damages of any kind. All Laird products are sold pursuant to the Laird Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2018 Laird Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Logo, and other marks are trademarks or registered trademarks of Laird Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird or any third party intellectual property rights.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[OD58M-12](#) [OD24-9D7](#)