







THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHT REVERSED ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
B2		ECR-21-108676		03AUG2021	LZ	FL	
C		ECR-21-110755		02SEP2021	KD	FL	



- HOUSING HAS RAST 5 COMPLIANT KEYING LATCHING, AND POLARIZATION, TAB IS 6.30 x 0.8mm ACCORDING TO DIN 46224
- MATERIAL: HOUSING NYLON, UL94 V0, 750 °C GWT NO FLAME
- FINISH: CONTACTS, TIN PLATING OVERALL , NICKEL UNDER-PLATING
- PACKING: LOOSE PIECE OR TUBE. THE PART NUMBER IN THIS DRAWING ARE WITH LOOSE PIECE PACKING. PLEASE CONTACT TE SALES REPRESENTATIVES FOR TUBE PACKING REQUIREMENT.
- PRELIMINARY, NOT FOR PRODUCTION.
- MATERIAL: HOUSING PA66, UL94 V0
PRODUCT COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30 (GWT).
- FINISH: CONTACT, SILVER PLATING OVERALL, NICKEL UNDER-PLATING.
- SPECIAL VERSION: SHORT PEG DESIGN, DETAIL IN SHEET 3
- PART NUMBER WITH TUBE PACKAGING.
- MATERIAL: PA66 GF, UL94 V0, 750°C GWT NO FLAME



42.30	40.30	8
37.30	35.30	7
32.30	30.30	6
27.30	25.30	5
22.30	20.30	4
17.30	15.30	3
12.30	10.30	2
N	M	NO.OF POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	B.P	APR162013
CHK	F.M	APR162013
APVD	-	APR162013
PRODUCT SPEC	108-106080	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 4

TE Connectivity


NAME RAST 5 TAB HEADER ASSY
DIN STYLE, TH, VERTICAL

SIZE A2 CAGE CODE 00779 DRAWING NO C-2232511 RESTRICTED TO


REV C

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHT REVERSED ALL RIGHTS RESERVED.


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
-	-	SEE SHEET 1	-	-	-		




3-2232511-3 $\Delta_5 \Delta_7$



4-2232511-5 Δ_9




2-2232511-3 Δ_5




2232511-3
 1-2232511-3 Δ_6
 2328608-3 Δ_8


3 POS.




2232511-4



1-2232511-4




2232511-5
 1-2232511-5 Δ_6
 2328608-5 Δ_8




2-2232511-5 Δ_5

5 POS.




2232511-6


6 POS.







VOID PIN




4 POS.




PCB LAYOUT SKETCH
 SOLDER SIDE



2232511-7
 1-2232511-7 Δ_6
 2328608-7 Δ_8




2-2232511-7 Δ_6
 1-2328608-7 Δ_8





3-2232511-7

7 POS.



2232511-8

8 POS.




PCB LAYOUT SKETCH
 SOLDER SIDE


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.P.	APR162013	TE Connectivity	
DIMENSIONS: mm		CHK	24SEP2013		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	24SEP2013	NAME RAST 5 TAB HEADER ASSY DIN STYLE, TH, VERTICAL	
0 PLC ±		PRODUCT SPEC		SIZE	
1 PLC ±0.5		108-106080		CAGE CODE	
2 PLC ±0.13		APPLICATION SPEC		DRAWING NO	
3 PLC ±0.013		WEIGHT		RESTRICTED TO	
4 PLC ±0.0001		CUSTOMER DRAWING		A200779	
ANGLES ±		SCALE 4:1		SHEET 2 OF 4	
FINISH		REV C			

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHT REVERSED ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
-	-	SEE SHEET 1	-	-	-		




THE POSITION OF THE 4 PIN TAIL HOLE AND POST ARE FIXED



PICTORIAL VIEW KEY

RECOMMEND PCB LAYOUT - SOLDER SIDE
 PCB 1.5± 0.2 THICK

COLOR	NO. OF POS.	PART NUMBER
	8	2232511-8
	7	3-2232511-7
	7	2-2232511-7
	7	1-2232511-7
	7	2232511-7
	6	2232511-6
	5	4-2232511-5
	5	2-2232511-5
	5	1-2232511-5
	5	2232511-5
	4	1-2232511-4
	4	2232511-4
	3	3-2232511-3
	3	2-2232511-3
	3	1-2232511-3
	3	2232511-3





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.P. APR162013	STE TE Connectivity	
		CHK - 24SEP2013		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD - 24SEP2013	NAME RAST 5 TAB HEADER ASSY DIN STYLE, TH, VERTICAL	
	0 PLC ±	PRODUCT SPEC 108-106080	SIZE A2	CAGE CODE 00779
	1 PLC ±0.5	APPLICATION SPEC	DRAWING NO C-2232511	RESTRICTED TO
MATERIAL -	FINISH -	WEIGHT -	SCALE 4:1	SHEET 3 OF 4
CUSTOMER DRAWING			REV C	

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHT REVERSED ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
-	-	SEE SHEET 1	-	-	-		

△ SPECIAL VERSION: SHORT PEG DESIGN



OTHER DIMENSIONS SEE SHEET 1
 KEYING SEE SHEET 2

NATURE	7	△ 1-2328608-7
	7	2328608-7
	5	2328608-5
	3	2328608-3
COLOR	NO. OF POS.	△ PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	APR162013	TE Connectivity					
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK	APR162013						
mm	0 PLC ±	F M	APR162013						
	1 PLC ±0.5	APVD	APR162013						
MATERIAL	FINISH	PRODUCT SPEC	108-106080	NAME	RAST 5 TAB HEADER ASSY DIN STYLE, TH, VERTICAL				
-	-	APPLICATION SPEC	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
-	-	WEIGHT	-	A2	00779	C-2232511	-		
-	-	CUSTOMER DRAWING	-	SCALE	4:1	SHEET	4 OF 4	REV	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2232511-5](#)