


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	08MAY2020	M. J	E. I

- 1

GOLD PLATING UNDER Ni PLATING
- 2

TIN PLATING UNDER Ni PLATING



P/N										
6-2260661-1	4-2260661-2	4-2260661-1								
2	2	2	2		COPPER ALLOY			RETENTION LEG	4	
6	4	4	1 2		COPPER ALLOY			CONTACT	3	
1					THERMO PLASTIC, POLYESTER (UL94V-0), COLOR: BLACK	X	6	HOUSING	2	
	1				THERMO PLASTIC, POLYESTER (UL94V-0), COLOR: BLACK	Y	4	HOUSING	1	
		1			THERMO PLASTIC, POLYESTER (UL94V-0), COLOR: BLACK	X	4	HOUSING	1	
QTY			FINISH		MATERIAL		KEY	POS	NAME	
									ITEM	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.3
1 PLC ±0.3
2 PLC ±0.3
3 PLC ±0.3
4 PLC ±0.3
ANGLES ±3°

MATERIAL
SEE TABLE

FINISH
SEE TABLE

DWN
M. JIANG
08MAY2020

CHK
T. SHIMOYASU
08MAY2020

APVD
E. IKEMATSU
08MAY2020

PRODUCT SPEC
108-140022

APPLICATION SPEC
408-78067

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
DYNAMIC D5900
HEADER ASSEMBLY

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2260661

RESTRICTED TO
-

SCALE
1:1







SHEET
1

OF
4


REV
A

1470-19 (3/13)

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-









REFERENCE PCB BOARD LAYOUT
PCB THICKNESS: 1.6~2.4±0.1
GENERAL TOLERANCE: ±0.05




4-2260661-1 (4POS KEY:X)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. JIANG 08MAY2020	 TE Connectivity		
		CHK T. SHIMOYASU 08MAY2020			
		APVD F. IKEMATSU 08MAY2020	NAME DYNAMIC D5900 HEADER ASSEMBLY		
		PRODUCT SPEC 108-140022			
		APPLICATION SPEC 408-78067			
		WEIGHT -			
		CUSTOMER DRAWING			
		SCALE 1:1			
		SHEET 2 OF 4			
		REV A			


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-









REFER TO SHEET2 FOR THE DIMENSIONS WHICH ARE NOT INDICATED ON THIS SHEET.



4-2260661-2(4POS KEY:Y)


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. JIANG 08MAY2020	 TE Connectivity		
DIMENSIONS: mm		CHK T. SHIMOYASU 08MAY2020			
		APVD F. IKEMATSU 08MAY2020	NAME DYNAMIC D5900 HEADER ASSEMBLY		
		PRODUCT SPEC 108-140022	SIZE A300779		
MATERIAL SEE SHEET 1		APPLICATION SPEC 408-78067	CAGE CODE C-2260661		RESTRICTED TO -
FINISH SEE SHEET 1		WEIGHT -	DRAWING NO C-2260661		REV A
CUSTOMER DRAWING		SCALE 1:1		SHEET 3 OF 4	


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



REFERENCE PCB BOARD LAYOUT
PCB THICKNESS: 1.6~2.4±0.1
GENERAL TOLERANCE: ±0.05

6-2260661-1 (6POS KEY:X)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. JIANG 08MAY2020	 TE Connectivity		
DIMENSIONS: mm		CHK T. SHIMOYASU 08MAY2020			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME DYNAMIC D5900 HEADER ASSEMBLY		
	0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.3 3 PLC ±0.3 4 PLC ±0.3 ANGLES ±3*				
	MATERIAL SEE SHEET 1		FINISH SEE SHEET 1		RESTRICTED TO -
CUSTOMER DRAWING			SIZE A3	CAGE CODE 00779	DRAWING NO C-2260661
			SCALE 1:1	SHEET 4 OF 4	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2260661-1](#)