






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		REMOVE PRELIMINARY NOTE	28AUG2019	CJ	CJ
A2		REMOVE PRELIMINARY WATERMARK	29AUG2019	CJ	CJ
A3		REV PER ECO-21-005543	04MAY2021	CMJ	CMJ
A4		ECN-22-144744	17MAR2022	SN	CJ

- 1 LASER MARK JULIAN DATE CODE APPROXIMATELY AS SHOWN
- 2 CIRCUIT IDENTIFICATION
3. MATING PART NUMBER: 2315564-1 THRU -4
4. 2315562-1 SHOWN IN GENERAL VIEWS
5. NOTE REMOVED
- 6 HOUSING MATERIAL: PA66-GF25
- 7 MATERIAL: BASE MATERIAL: BRASS.
PLATING: CONTACT AREA: 1.5-3.0µm TIN WITH
2.0µm MIN NICKEL UNDERPLATE.
SOLDER TAIL AREA: 2.5µm MIN TIN WITH
2.0µm MIN NICKEL UNDERPLATE.
- 8 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 9 HOUSING MATERIAL: PA66-GF30
- 10 PENDING OBSOLESCENCE




10	10	10	10	10	10	10	10	7	PINS, 0.64X0.64	N/A	2
1	-	-	-	-	-	-	-	9	HOUSING, KEY D	BLUE	1
-	1	-	-	-	-	-	-		HOUSING, KEY C	GREEN	1
-	-	1	-	-	-	-	-		HOUSING, KEY B	GRAY	1
-	-	-	1	-	-	-	-		HOUSING, KEY A	TAN	1
-	-	-	-	1	-	-	-	6	HOUSING, KEY D	BLUE	1
-	-	-	-	-	1	-	-		HOUSING, KEY C	GREEN	1
-	-	-	-	-	-	1	-		HOUSING, KEY B	GRAY	1
-	-	-	-	-	-	-	1		HOUSING, KEY A	TAN	1
1-2315562-4	1-2315562-3	1-2315562-2	1-2315562-1	2315562-4	2315562-3	2315562-2	2315562-1	MATERIAL	DESCRIPTION	COLOR	ITEM NO.
QUANTITY REQUIRED PER ASSEMBLY											


QUANTITY REQUIRED PER ASSEMBLY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: TISHA MINGO-ODUROTE CHK: RIDDHI KHINVASARA APVD: GALEN MARTIN	01MAY2017 01MAY2017 01MAY2017
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED	PRODUCT SPEC	NAME
mm	0 PLC ±.5 1 PLC ±.5 2 PLC ±.5 3 PLC ±.5 4 PLC ±.5 HOLE FINISH	APPLICATION SPEC	10POS,TAB0.64X0.64,HDR ASSY, 180DEG,SLDR
MATERIAL	SEE TABLE	WEIGHT	SIZE
-	-	6.01g	CAGE CODE
CUSTOMER DRAWING		SCALE	DRAWING NO
		5:1	2315562
		SHEET	RESTRICTED TO
		1 OF 2	-
		REV	A4


KEY CODE A




KEY CODE B






KEY CODE C



KEY CODE D



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED

0 PLC	±.5
1 PLC	±.5
2 PLC	±0.13
3 PLC	±0.013
4 PLC	±0.0001
HOLES	±.1
FINISH	-

01MAY2017
TISHA MINGO-ODUROTE
01MAY2017
RIDDHI KHINVASARA
01MAY2017
CALEN MARTIN

NAME

10POS,TAB0.64X0.64,HDR ASSY,
180DEG,SLDR

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

WEIGHT

6.01g

SCALE

5:1

SHEET

2

OF

2

REV

A4

APVD

SALEN MARTIN

PRODUCT SPEC

APPLICATION SPEC

CUSTOMER DRAWING

DWN

01MAY2017

CHK

01MAY2017

NAME

10POS,TAB0.64X0.64,HDR ASSY,
180DEG,SLDR

SCALE

5:1

SHEET

2

OF

2

REV

A4

TE Connectivity

2315562

4805 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2315562-2](#)