






LOC		DIST		REVISIONS						
IN	00	P	LTR	DESCRIPTION				DATE	DWN	APVD
		A		REV PER ECO-17-009112				17JUL2017	HM	CR
		A1		REV PER ECO-19-008549				08JUL2019	SY	CR



- △ COPPER ALLOY
- 2 2.0μm MIN SILVER IN ZONE 1, 0.5μm MIN SILVER IN WIRE BARREL ALL OVER 0.5μm NICKEL
3. TERMINAL DESIGNED TO BE USED WITH SINGLE WIRE SEAL. SEE APPLICATION SPEC 114-32121 FOR PART NUMBERS
4. MAX 9 TERMINALS MISSING PER REEL PERMITTED
5. 3 LOOSE SPLICES PER REEL ALLOWED
6. SEE APPLICATION SPEC 114-32121 FOR ALLOWABLE INSULATION O.D.
- A1 7. TERMINAL IS QUALIFIED TO GMW3191 T3(-40°C TO 125°C) AND V1(SEALED ON BODY SPRUNG MASS)



SECTION AN-AN
SCALE 20:1



SECTION AP-AP
SCALE 20:1




FIG 1
REELING DIRECTION
SCALE 3:1

0.220	FIG 1	1.80	1.80	0.80	4.20	2.60	2.60	6.40	0.35mm ²	2-2321973-3
0.230	FIG 1	2.00	2.10	1.10	4.20	2.70	3.00	6.80	0.50mm ²	2-2321973-2
0.235	FIG 1	2.40	2.77	1.10	4.40	2.90	3.00	6.80	0.75mm ² TO 1.0mm ²	2-2321973-1
WEIGHT (GRAMS)	REELING	G	F	E	D	C	B	A	WIRE SIZE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN H. MOLL	17JUL2017	 TE Connectivity			
				CHK C. RAYBOLD	17JUL2017				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. RAYBOLD	17JUL2017	NAME			
mm		0 PLC ±		PRODUCT SPEC		MALE TERMINAL, SILVER PLATED, MCON MONO 1.2			
		1 PLC ±		108-32199					
		2 PLC ±		APPLICATION SPEC		SIZE			
		3 PLC ±		SEE NOTES		CAGE CODE			
		4 PLC ±		ANGLES		DRAWING NO			
MATERIAL		FINISH		WEIGHT		RESTRICTED TO			
: 		: 		SEE TABLE		A1		00779C=2321973	
CUSTOMER DRAWING				SCALE		10:1		SHEET 1 OF 1	
								REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2321973-2](#)