


REVISIONS				
P	LTR	DESCRIPTION	DATE	APP'D
G		REVISED PER ECO-21-005294	07MAY2021	KK AK



1. CHARACTERISTIC IMPEDANCE: 100±10 OHMS (MEASURED DIFFERENTIALLY)

2 LABEL INFORMATION FOR 25 GIG PNS (-1 THRU -8): -1 SHOWN



3. SEE SHEET 2 FOR WIRING SCHEMATIC.

4. ROHS COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE CONNECTIVITY SPECIFICATION TEC-138-702.

5 TEST IN ACCORDANCE WITH IEEE802.3by.

6 DASH NUMBER 41 THRU 45 CONFORM TO 56G, PAM-4 IEEE802.3CD PERFORMANCE REQUIREMENTS.

7 LABEL INFORMATION FOR 56 GIG PNS (-41 THRU -45): -41 SHOWN




6	26	3000	+80 -0	4-2821224-5
	26	2500	+80 -0	4-2821224-4
	26	2000	+80 -0	4-2821224-3
	26	1500	+80 -0	4-2821224-2
	26	1000	+50 -0	4-2821224-1
5	26	5000	+80 -0	2821224-8
	26	4000	+80 -0	2821224-7
	26	3500	+80 -0	2821224-6
	26	3000	+80 -0	2821224-5
	26	2500	+80 -0	2821224-4
	26	2000	+80 -0	2821224-3
	26	1500	+80 -0	2821224-2
	26	1000	+50 -0	2821224-1
STANDARD	WIRE GAGE	L	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN T. SMITH 08OCT2015	TE Connectivity Ltd.
0. PLC ±	1. PLC ±	CHK C. POGASH 08OCT2015	
2. PLC ±	3. PLC ±	APP'D G. POGASH 08OCT2015	NAME
4. PLC ±	ANGLES ±	PRODUCT SPEC	CABLE ASSY, 26 AWG, SFP+ TO SFP+, 28GIG
MATERIAL	FINISH	APPLICATION SPEC	RESTRICTED TO
		SIZE CAGE CODE DRAWING NO	A1 00779 C=2821224
		WEIGHT 0	CUSTOMER DRAWING
		SCALE 1:1	SHEET 1 OF 2

REVISIONS				
REV	DATE	DESCRIPTION	BY	APP'D
1		SEE SHEET 1		



THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN T.SMITH 08OCT2015	TE Connectivity Ltd.	
DIMENSIONS: mm		CHK C.POGASH 08OCT2015	NAME CABLE ASSY,26 AWG,SFP+ TO SFP+, 28GIG	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± - 1. PLC ± - 2. PLC ± - 3. PLC ± - 4. PLC ± - ANGLES ± -		APP'D C.POGASH 08OCT2015	PRODUCT SPEC	
MATERIAL		APPLICATION SPEC	SIZE A1	RESTRICTED TO
FINISH		WEIGHT	CAGE CODE 00779	DRAWING NO 2821224
		CUSTOMER DRAWING	SCALE 1:1	SHEET 2 of 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2821224-1](#)