



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11FEB2016 RAKSHITH NAYAK CHR 01APR2016 KARTHIK J K APVD 01APR2016 PRASHANTH S		 TE Connectivity		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.1 2 PLC ±0.05 3 PLC ± 4 PLC ± ANGLES ±2° FINISH		NAME AMPMODU 2mm SHROUDED HEADER, DUAL ROW, RIGHT ANGLE		
		PRODUCT SPEC 108-64040				
MATERIAL SEE NOTES -		APPLICATION SPEC 114-64040				
WEIGHT -		SIZE A2		CAGE CODE 00779		
CUSTOMER DRAWING		DRAWING NO C-2823351		RESTRICTED TO -		
SCALE 8:1		SHEET 1 of 3		REV A3		

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

TE CONNECTIVITY

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

SMART PART NUMBER

2MM - HSD - D - HT - - - - -

PRODUCT SERIES

2MM AMPMODU 2mm series

GENDER / TYPE

HSD Shrouded headers for detent latch

NUMBER OF ROWS

D Double row

NUMBER OF PINS PER ROW

XX 02 through 16,20,22,25 (enter two digits)

ORIENTATION & TERMINATION

HT Horizontal through hole

PACKAGING

TB	Tube without cap	
TBP	Tube with cap	8
TRP	Tape and reel with cap	8
BX	Box	9

PLATING

T	Tin
F	0.1µm Gold (Gold flash)
M	0.38 µm Gold
H	0.76 µm Gold

TAIL LENGTH

01	2.2 mm
02	2.8 mm
03	3.4 mm

SMART PN EXAMPLES :

1. AMPMODU 2MM, SHROUDED HEADER STD VERSION, DOUBLE ROW , 02 POSITION PER ROW , RIGHT ANGLE MOUNT, 2.2MM SOLDER TAIL LENGTH, TIN PLATING, TUBE W/O CAP
2MM-HSD-D02-HT-01-T-TB

2. AMPMODU 2MM, SHROUDED HEADER STD VERSION, DOUBLE ROW , 25 POSITION PER ROW , RIGHT ANGLE MOUNT, 3.4MM SOLDER TAIL LENGTH, 0.76µm GOLD PLATING, BOX PACKAGING
2MM-HSD-D25-HT-03-H-BX

THIS PRINT IS

PRELIMINARY

UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.1

2 PLC ±0.05

3 PLC ±

4 PLC ±

ANGLES ±2°

FINISH

SEE NOTES

-

DWN 11FEB2016
CHK 01APR2016
APVD 01APR2016
PRODUCT SPEC
APPLICATION SPEC
WEIGHT

RAKSHITH NAYAK
KARTHIK J K
PRASHANTH S

108-64040
114-64040
-

CUSTOMER DRAWING

TE Connectivity

NAME
AMPMODU 2mm SHROUDED HEADER,
DUAL ROW , RIGHT ANGLE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=2823351

RESTRICTED TO
-

SCALE
1:1

SHEET
3 OF 3

REV
A3

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2823351-8](#)