





2	96.52[3.800]	99.06[3.900]	78	4–534267–0
2	91.44[3.600]	93.98[3.700]	74	3–534267–9
2	88.90[3.500]	91.44[3.600]	72	3–534267–8
2	86.36[3.400]	88.90[3.500]	70	3–534267–7
2	83.82[3.300]	86.36[3.400]	68	3–534267–6
2	81.28[3.200]	83.82[3.300]	66	3–534267–5
2	78.74[3.100]	81.28[3.200]	64	3–534267–4
2	76.20[3.000]	78.74[3.100]	62	3–534267–3
2	71.12[2.800]	73.66[2.900]	58	3–534267–2
2	68.58[2.700]	71.12[2.800]	56	3–534267–1
2	66.04[2.600]	68.58[2.700]	54	3–534267–0
2	63.50[2.500]	66.04[2.600]	52	2–534267–9
2	55.88[2.200]	58.42[2.300]	46	2–534267–8
2	53.34[2.100]	55.88[2.200]	44	2–534267–7
2	50.80[2.000]	53.34[2.100]	42	2–534267–6
2	45.72[1.800]	48.26[1.900]	38	2–534267–5
2	40.64[1.600]	43.18[1.700]	34	2–534267–4
2	38.10[1.500]	40.64[1.600]	32	2–534267–3
2	33.02[1.300]	35.56[1.400]	28	2–534267–2
2	25.40[1.000]	27.94[1.100]	22	2–534267–1
2	12.70[.500]	15.24[.600]	12	2–534267–0
2	17.78[.700]	20.32[.800]	16	1–534267–9
2	60.96[2.400]	63.50[2.500]	50	1–534267–8
2	2.54[.100]	5.08[.200]	4	1–534267–7
2	93.98[3.700]	96.52[3.800]	76	1–534267–6
2	43.18[1.700]	45.72[1.800]	36	1–534267–5
2	5.08[.200]	7.62[.300]	6	1–534267–4
10	2.54[.100]	2.54[.100]	2	1–534267–3
2	35.56[1.400]	38.10[1.500]	30	1–534267–2
2	58.42[2.300]	60.96[2.400]	48	1–534267–1
2	20.32[.800]	22.86[.900]	18	1–534267–0
2	27.94[1.100]	30.48[1.200]	24	534267–9
2	73.66[2.900]	76.20[3.000]	60	534267–8
2	48.26[1.900]	50.80[2.000]	40	534267–7
2	30.48[1.200]	33.02[1.300]	26	534267–6
10	7.62[.300]	10.16[.400]	8	534267–5
2	99.06[3.900]	101.60[4.000]	80	534267–4
10	10.16[.400]	12.70[.500]	10	534267–3
2	22.86[.900]	25.40[1.000]	20	534267–2
2	15.24[.600]	17.78[.700]	14	534267–1

FINISH	B	A	NO OF POSN	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		
		0 PLC ± –		
		1 PLC ± –		
		2 PLC ± 0.13[.005]		
		3 PLC ± –		
		4 PLC ± –		
		ANGLES ± –		
MATERIAL		FINISH		
1		11 2		
		DWN M.BINNER 06NOV2002		
		CHK J.OLSON 06NOV02		
		APVD J.OLSON 06NOV02		
		PRODUCT SPEC		
		108–25022		
		APPLICATION SPEC		
		114–25018		
		WEIGHT –		
		CUSTOMER DRAWING		
		SCALE 4:1		
		SHEET 1 OF 2		
		REV AC		
		NAME		
		RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU		
		SIZE		
		A2		
		CAGE CODE		
		00779		
		DRAWING NO		
		C=534267		
		RESTRICTED TO		
		–		

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

	\triangle_{11}	96.52[3.800]	99.06[3.900]	78	\triangle_{12}	9-534267-0
	\triangle_{11}	91.44[3.600]	93.98[3.700]	74	\triangle_{12}	8-534267-9
	\triangle_{11}	88.90[3.500]	91.44[3.600]	72	\triangle_{12}	8-534267-8
	\triangle_{11}	86.36[3.400]	88.90[3.500]	70	\triangle_{12}	8-534267-7
	\triangle_{11}	83.82[3.300]	86.36[3.400]	68	\triangle_{12}	8-534267-6
	\triangle_{11}	81.28[3.200]	83.82[3.300]	66	\triangle_{12}	8-534267-5
	\triangle_{11}	78.74[3.100]	81.28[3.200]	64	\triangle_{12}	8-534267-4
	\triangle_{11}	76.20[3.000]	78.74[3.100]	62	\triangle_{12}	8-534267-3
	\triangle_{11}	71.12[2.800]	73.66[2.900]	58	\triangle_{12}	8-534267-2
	\triangle_{11}	68.58[2.700]	71.12[2.800]	56	\triangle_{12}	8-534267-1
	\triangle_{11}	66.04[2.600]	68.58[2.700]	54	\triangle_{12}	8-534267-0
	\triangle_{11}	63.50[2.500]	66.04[2.600]	52	\triangle_{12}	7-534267-9
	\triangle_{11}	55.88[2.200]	58.42[2.300]	46	\triangle_{12}	7-534267-8
	\triangle_{11}	53.34[2.100]	55.88[2.200]	44	\triangle_{12}	7-534267-7
	\triangle_{11}	50.80[2.000]	53.34[2.100]	42	\triangle_{12}	7-534267-6
	\triangle_{11}	45.72[1.800]	48.26[1.900]	38	\triangle_{12}	7-534267-5
	\triangle_{11}	40.64[1.600]	43.18[1.700]	34	\triangle_{12}	7-534267-4
	\triangle_{11}	38.10[1.500]	40.64[1.600]	32	\triangle_{12}	7-534267-3
	\triangle_{11}	33.02[1.300]	35.56[1.400]	28	\triangle_{12}	7-534267-2
	\triangle_{11}	25.40[1.000]	27.94[1.100]	22	\triangle_{12}	7-534267-1
	\triangle_{11}	12.70[.500]	15.24[.600]	12	\triangle_{12}	7-534267-0
	\triangle_{11}	17.78[.700]	20.32[.800]	16	\triangle_{12}	6-534267-9
\triangle_{10}	\triangle_{11}	60.96[2.400]	63.50[2.500]	50	\triangle_{12}	6-534267-8
	\triangle_{11}	2.54[.100]	5.08[.200]	4	\triangle_{12}	6-534267-7
	\triangle_{11}	93.98[3.700]	96.52[3.800]	76	\triangle_{12}	6-534267-6
\triangle_{10}	\triangle_{11}	43.18[1.700]	45.72[1.800]	36	\triangle_{12}	6-534267-5
ETE	\triangle_{11}	5.08[.200]	7.62[.300]	6	\triangle_{12}	6-534267-4
	\triangle_{11}	-	2.54[.100]	2	\triangle_{12} \triangle_6	6-534267-3
	\triangle_{11}	35.56[1.400]	38.10[1.500]	30	\triangle_{12}	6-534267-2
	\triangle_{11}	58.42[2.300]	60.96[2.400]	48	\triangle_{12}	6-534267-1
	\triangle_{11}	20.32[.800]	22.86[.900]	18	\triangle_{12}	6-534267-0
	\triangle_{11}	27.94[1.100]	30.48[1.200]	24	\triangle_{12}	5-534267-9
	\triangle_{11}	73.66[2.900]	76.20[3.000]	60	\triangle_{12}	5-534267-8
	\triangle_{11}	48.26[1.900]	50.80[2.000]	40	\triangle_{12}	5-534267-7
	\triangle_{11}	30.48[1.200]	33.02[1.300]	26	\triangle_{12}	5-534267-6
\triangle_{10}	\triangle_{11}	7.62[.300]	10.16[.400]	8	\triangle_{12}	5-534267-5
	\triangle_{11}	99.06[3.900]	101.60[4.000]	80	\triangle_{12}	5-534267-4
\triangle_{10}	\triangle_{11}	10.16[.400]	12.70[.500]	10	\triangle_{12}	5-534267-3
	\triangle_{11}	22.86[.900]	25.40[1.000]	20	\triangle_{12}	5-534267-2
	\triangle_{11}	15.24[.600]	17.78[.700]	14	\triangle_{12}	5-534267-1
	FINISH	B	A	NO OF POSN		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV0202		 TE Connectivity Ltd.	
		CHK J.OLSON 06NOV02			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
		APVD J.OLSON 06NOV02			
		PRODUCT SPEC 108-25022			
		APPLICATION SPEC 114-25018			
MATERIAL 		FINISH 		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
		WEIGHT -		A2 00779 C-534267 -	
CUSTOMER DRAWING				SCALE 1:1 SHEET 2 of 2 REV AC	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-534267-4](#)