



6	0.6	±0.40	108.44	110.94	21	3-284065-3
6	0.4	±0.25	77.96	80.46	15	3-284065-2
6	0.6	±0.40	83.08	85.58	16	3-284065-1
6		±0.50	123.68	126.18	24	3-284065-0
6			123.68	126.18	24	2-284065-9
6		±0.40	93.20	95.70	18	2-284065-8
6			83.08	85.58	16	2-284065-7
6		0.4	±0.25	62.72	65.22	12
6	0.6	±0.50	128.80	131.30	25	2-284065-5
		±0.40	123.68	126.18	24	2-284065-4
			118.64	121.14	23	2-284065-3
			113.56	116.06	22	2-284065-2
			108.44	110.94	21	2-284065-1
			103.40	105.90	20	2-284065-0
			98.32	100.82	19	1-284065-9
			93.20	95.70	18	1-284065-8
	88.16	90.66	17	1-284065-7		
	83.08	85.58	16	1-284065-6		
	0.4	±0.25	77.96	80.46	15	1-284065-5
			72.92	75.42	14	1-284065-4
			67.84	70.34	13	1-284065-3
			62.72	65.22	12	1-284065-2
			57.68	60.18	11	1-284065-1
			52.60	55.10	10	1-284065-0
	0.3	±0.20	47.48	49.98	9	284065-9
			42.44	44.94	8	284065-8
			37.36	39.86	7	284065-7
			32.24	34.74	6	284065-6
			27.20	29.70	5	284065-5
			22.16	24.66	4	284065-4
	0.1	±0.15	17.00	19.50	3	284065-3
			12.00	14.50	2	284065-2
CURVATURE MAX DIM "C" (SHEET 2)		DIM "A" TOL	DIM "A"	DIM "B"	POS	PART NUMBER



5. P/N FROM 284065-4 TO 2-284065-5 ARE OBTAINED BY ASSEMBLING DIFFERENT MONOLITHIC MODULES CHOSEN AMONG: 284065-2 AND 284065-3, IN ORDER TO REALIZE THE DESIRED NO. OF WAYS.


△₆ MODULES AND KEYS TO BE GLUED IN PLACE.

 NON CUMULATIVE TOLERANCE


264065-3 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 07MAR2008 S SCHLEGEL		 TE Connectivity	
		CHK 03JUL2008 C RICHARD			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL BLOCK, MULTIPLE HEADER. 180 DEGREE, CLOSED ENDS, 5.08mm PITCH	
mm		APVD 03JUL2008 C RICHARD			
		PRODUCT SPEC			
		-			
		APPLICATION SPEC		SIZE	
		114-20079		CAGE CODE	
MATERIAL		FINISH		DRAWING NO	
				RESTRICTED TO	
		WEIGHT		A2 00779 C=284065	
		-		-	
CUSTOMER DRAWING				SCALE 5:1	
				SHEET 1 OF 4	
				REV F	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




2-284065-6




2-284065-9



2-284065-7



2-284065-8



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±0.25

3 PLC ±-

4 PLC ±-

ANGLES ±2°

FINISH

DWN 07MAR2008
S SCHLEGEL
CHK 03JUL2008
C RICHARD
APVD 03JUL2008
C RICHARD
PRODUCT SPEC
APPLICATION SPEC
114-20079
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL BLOCK, MULTIPLE HEADER.
180 DEGREE, CLOSED ENDS,
5.08mm PITCH

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-284065


RESTRICTED TO
-

SCALE 5:1


SHEET 2 OF 4

REV E1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



3-284065-0



3-284065-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±0.25

3 PLC ±-

4 PLC ±-

ANGLES ±2°

FINISH

DWN 07MAR2008
S SCHLEGEL
CHK 03JUL2008
C RICHARD
APVD 03JUL2008
C RICHARD
PRODUCT SPEC
APPLICATION SPEC
114-20079
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL BLOCK, MULTIPLE HEADER.
180 DEGREE, CLOSED ENDS,
5.08mm PITCH

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-284065


RESTRICTED TO
-

SCALE 5:1

SHEET 3 OF 4

REV E1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±0.25

3 PLC ±-

4 PLC ±-

ANGLES ±2°

FINISH

DWN
S. SCHLEGEL
07MAR2008

CHK
C. RICHARD
03JUL2008

APVD
C. RICHARD
03JUL2008

PRODUCT SPEC
-

APPLICATION SPEC
114-20079

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL BLOCK, MULTIPLE HEADER.
180 DEGREE, CLOSED ENDS,
5.08mm PITCH

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-284065

RESTRICTED TO
-

SCALE
5:1

SHEET
4 OF 4

REV
E1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[284065-6](#)