

6	0.6	±0.40	108.44	110.94	21	3-284065-3
6	0.4	±0.25	77.96	80.46	15	3-284065-2
6	0.6	±0.40	83.08	85.58	16	3-284065-1
6			±0.50	123.68	126.18	24
6		123.68		126.18	24	2-284065-9
6		±0.40	93.20	95.70	18	2-284065-8
6			83.08	85.58	16	2-284065-7
6		0.4	±0.25	62.72	65.22	12
6	0.6	±0.50	128.80	131.30	25	2-284065-5
			123.68	126.18	24	2-284065-4
		±0.40	118.64	121.14	23	2-284065-3
			113.56	116.06	22	2-284065-2
			108.44	110.94	21	2-284065-1
			103.40	105.90	20	2-284065-0
			98.32	100.82	19	1-284065-9
			93.20	95.70	18	1-284065-8
	88.16	90.66	17	1-284065-7		
	83.08	85.58	16	1-284065-6		
	0.4	±0.25	77.96	80.46	15	1-284065-5
			72.92	75.42	14	1-284065-4
			67.84	70.34	13	1-284065-3
			62.72	65.22	12	1-284065-2
			57.68	60.18	11	1-284065-1
			52.60	55.10	10	1-284065-0
	0.3	±0.20	47.48	49.98	9	284065-9
			42.44	44.94	8	284065-8
			37.36	39.86	7	284065-7
			32.24	34.74	6	284065-6
			27.20	29.70	5	284065-5
			22.16	24.66	4	284065-4
	0.1	±0.15	17.00	19.50	3	284065-3
			12.00	14.50	2	284065-2
CURVATURE MAX DIM "C" (SHEET 2)		DIM "A" TOL	DIM "A"	DIM "B"	POS	PART NUMBER

1. MATERIALS AND FINISH:
HOUSING: HIGH TEMPERATURE POLYAMIDE, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.

2. SUITABLE FOR 1.6-2.4mm PC BOARD THK.


3. ELECTRICAL
RATED VOLTAGE : 300 V
RATED CURRENT : 12 A
CONTACT RESISTANCE : < 15 mΩ
INSULATION RESISTANCE: > 1000 MΩ (500V DC)

4. OPERATING TEMPERATURE RANGE: -40°C TO +110°C


5. P/N FROM 284065-4 TO 2-284065-5 ARE OBTAINED
BY ASSEMBLING DIFFERENT MONOLITHIC MODULES
CHOSEN AMONG: 284065-2 AND 284065-3, IN ORDER
TO REALIZE THE DESIRED NO. OF WAYS.

6 MODULES AND KEYS TO BE GLUED IN PLACE.



 NON CUMULATIVE TOLERANCE






264065-3 AS SHOWN



RECOMMENDED PC BOARD LAYOUT




		TE Connectivity	
NAME TERMINAL BLOCK, MULTIPLE HEADER. 180 DEGREE, CLOSED ENDS, 5.08mm PITCH			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	Ⓒ-284065	-
		SCALE	SHEET
		5:1	2 OF 4
		REV	E1




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGE	07MAR2008		 TE Connectivity				
		CHK C. RICHARD	03JUL2008						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.3 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±.3 4 PLC ±.3 ANGLES ±2°		APVD C. RICHARD	NAME TERMINAL BLOCK, MULTIPLE HEADER. 180 DEGREE, CLOSED ENDS, 5.08mm PITCH				
		PRODUCT SPEC -							
MATERIAL		APPLICATION SPEC 114-20079		SIZE A2			CAGE CODE 00779	DRAWING NO C-284065	RESTRICTED TO -
FINISH		WEIGHT -							
CUSTOMER DRAWING					SCALE 5:1	SHEET 2 of 4	REV E1		


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




3-284065-0




3-284065-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 07MAR2008	 TE Connectivity			
DIMENSIONS: mm		CHK C RICHARD 03JUL2008				
		APVD C RICHARD 03JUL2008	NAME TERMINAL BLOCK, MULTIPLE HEADER. 180 DEGREE, CLOSED ENDS, 5.08mm PITCH			
		PRODUCT SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C-284065	RESTRICTED TO -
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±- 4 PLC ±- ANGLES ±2° FINISH		APPLICATION SPEC 114-20079	SCALE 5:1			
MATERIAL		WEIGHT -	SHEET 3 OF 4			
CUSTOMER DRAWING			REV E1			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-



3-284065-2



3-284065-3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 07MAR2008	 TE Connectivity			
DIMENSIONS: mm		CHK C. RICHARD 03JUL2008				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±- 4 PLC ±- ANGLES ±2° FINISH		APVD C. RICHARD 03JUL2008	NAME TERMINAL BLOCK, MULTIPLE HEADER. 180 DEGREE, CLOSED ENDS, 5.08mm PITCH			
MATERIAL		PRODUCT SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C-284065	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 5:1	SHEET 4 OF 4	REV E1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[284065-7](#)