

6	0.6	±0.40	108.44	110.94	21	3-284065-3
6	0.4	±0.25	77.96	80.46	15	3-284065-2
6	0.6	±0.40	83.08	85.58	16	3-284065-1
6			123.68	126.18	24	3-284065-0
6		±0.50	123.68	126.18	24	2-284065-9
6			93.20	95.70	18	2-284065-8
6		±0.40	83.08	85.58	16	2-284065-7
6			62.72	65.22	12	2-284065-6
6	0.4	±0.25	62.72	65.22	12	2-284065-6
6	0.6	±0.50	128.80	131.30	25	2-284065-5
			123.68	126.18	24	2-284065-4
		±0.40	118.64	121.14	23	2-284065-3
			113.56	116.06	22	2-284065-2
			108.44	110.94	21	2-284065-1
			103.40	105.90	20	2-284065-0
			98.32	100.82	19	1-284065-9
			93.20	95.70	18	1-284065-8
			88.16	90.66	17	1-284065-7
			83.08	85.58	16	1-284065-6
	0.4	±0.25	77.96	80.46	15	1-284065-5
			72.92	75.42	14	1-284065-4
			67.84	70.34	13	1-284065-3
			62.72	65.22	12	1-284065-2
			57.68	60.18	11	1-284065-1
			52.60	55.10	10	1-284065-0
	0.3	±0.20	47.48	49.98	9	284065-9
			42.44	44.94	8	284065-8
			37.36	39.86	7	284065-7
			32.24	34.74	6	284065-6
			27.20	29.70	5	284065-5
			22.16	24.66	4	284065-4
	0.1	±0.15	17.00	19.50	3	284065-3
			12.00	14.50	2	284065-2
CURVATURE MAX DIM "C" (SHEET 2)		DIM "A" TOL	DIM "A"	DIM "B"	POS	PART NUMBER

1. MATERIALS AND FINISH:
HOUSING: HIGH TEMPERATURE POLYAMIDE, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.

2. SUITABLE FOR 1.6-2.4mm PC BOARD THK.


3. ELECTRICAL
RATED VOLTAGE : 300 V
RATED CURRENT : 12 A
CONTACT RESISTANCE : $< 15 \text{ m}\Omega$
INSULATION RESISTANCE: $> 1000 \text{ M}\Omega$ (500V DC)

4. OPERATING TEMPERATURE RANGE: -40°C TO $+110^{\circ}\text{C}$


5. P/N FROM 284065-4 TO 2-284065-5 ARE OBTAINED
BY ASSEMBLING DIFFERENT MONOLITHIC MODULES
CHOSEN AMONG: 284065-2 AND 284065-3, IN ORDER
TO REALIZE THE DESIRED NO. OF WAYS.

6 MODULES AND KEYS TO BE GLUED IN PLACE.


 NON CUMULATIVE TOLERANCE




264065-3 AS SHOWN




RECOMMENDED PC BOARD LAYOUT




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




2-284065-6




2-284065-9



2-284065-7




2-284065-8




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 07MAR2008	 TE Connectivity		
DIMENSIONS: mm		CHK C. RICHARD 03JUL2008			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.3 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±2° FINISH		APVD C. RICHARD 03JUL2008	NAME TERMINAL BLOCK, MULTIPLE HEADER. 180 DEGREE, CLOSED ENDS, 5.08mm PITCH		
MATERIAL		PRODUCT SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C-284065
		APPLICATION SPEC 114-20079	RESTRICTED TO -		
		WEIGHT -			
		CUSTOMER DRAWING	SCALE 5:1	SHEET 2 OF 4	REV E1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



3-284065-0



3-284065-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±0.25

3 PLC ±-

4 PLC ±-

ANGLES ±2°

FINISH

DWN
S SCHLEGEL
07MAR2008

CHK
C RICHARD
03JUL2008

APVD
C RICHARD
03JUL2008

PRODUCT SPEC
-

APPLICATION SPEC
114-20079

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL BLOCK, MULTIPLE HEADER.
180 DEGREE, CLOSED ENDS,
5.08mm PITCH

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-284065


RESTRICTED TO
-

SCALE
5:1


SHEET
3 OF 4

REV
E1


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-



3-284065-2



3-284065-3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 07MAR2008	 TE Connectivity			
DIMENSIONS: mm		CHK C. RICHARD 03JUL2008				
		APVD C. RICHARD 03JUL2008	NAME TERMINAL BLOCK, MULTIPLE HEADER. 180 DEGREE, CLOSED ENDS, 5.08mm PITCH			
		PRODUCT SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C-284065	RESTRICTED TO -
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±- 4 PLC ±- ANGLES ±2° FINISH		APPLICATION SPEC 114-20079	SCALE 5:1			
MATERIAL		WEIGHT -	SHEET 4 OF 4			
CUSTOMER DRAWING			REV E1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[284065-8](#)