

©

TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B4	ECR-22-127164	25JAN2022	T.Q	N.S

(AS SHOWN : -6)








Fig-1

- NOTES:
- PEELING RESISTANCE: 0.196N(20gf)-0.686N(70gf)
SPEED: 300mm/min

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

TOLERANCE UNLESS OTHERWISE SPECIFIED

10>* :±0.2
30>*>10 :±0.25
100>*>30 :±0.3
ANGLE :±3°

DWN JACH HOU 19SEP10
CHK MARTIN LI 19SEP10
APVD STEVEN YAO 19SEP10

PRODUCT SPEC
108-60016
APPLICATION SPEC
WEIGHT

CUSTOMER DRAWING


TE Connectivity Ltd.

EMBOSS
CT HEADER ASSY
BOX V SMT

SIZE A3
CAGE CODE 00779
DRAWING NO C-292175
SCALE N/A
SHEET 1 OF 3
REV B4


RESTRICTED TO

OBSOLETED	BLACK		44.0	40.50	20.25	25.60	9	2-292175-9
			44.0	40.4	20.2	22.9	8	2- -8
			32.0	28.4	14.2	20.9	7	2- -7
			32.0	28.4	14.2	18.9	6	2- -6
			32.0	28.4	14.2	16.9	5	2- -5
			32.0	28.4	14.2	14.9	4	2- -4
		WITH	32.0	28.4	14.2	12.9	3	2- -3
	NATURAL		44.0	40.50	20.25	25.60	9	292175-9
			44.0	40.4	20.2	22.9	8	-8
			32.0	28.4	14.2	20.9	7	-7
			32.0	28.4	14.2	18.9	6	-6
			32.0	28.4	14.2	16.9	5	-5
			32.0	28.4	14.2	14.9	4	-4
			32.0	28.4	14.2	12.9	3	-3
	WITH	32.0	28.4	14.2	10.9	700	2	292175-2
COLOR	PLATE	D	C	B	A	QTY/ REEL	POS	TAPING P/N




NOTES;

- ③ OCCUPANT AREA ON PC BOARD
④ TO BE MEASURED WITH CONNECTOR PLACED
ON HORIZONTAL DATUM SURFACE, FLOAT OF
SOLDER TINE AND TAIL FROM DATUM
SURFACE IS 0.1mm MAX



SECT "A"-"A"



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	
mm	
	
MATERIAL	
SEE NOTE	

TOLERANCES UNLESS OTHERWISE SPECIFIED:

PLC	± .001
PLC	± .001
PLC	± .001
PLC	± .001
PLC	± .001
GLS	± .001
NISH	± .001


SEE NOTE

DWN	—
CHK	—
APVD	—
PRODUCT SPEC	
108-60016	
APPLICATION SPEC	
WEIGHT	
CUSTOMER DRAWING	

TE Connectivity Ltd.

ON TAPING (EMBOSS)
SMT TYPE POST HDR ASS'Y(V)
W/O BOSS &WITH TAIL TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
A3	00779	C=292175	—	
		SCALE	SHEET	REV
		N/A	2 OF 3	R4



2. MATERIAL:HSG-NYLON (UL94V-0)
COLOR:NATURAL,BLACK
POST:TIN BRASS
TAIL: TIN BRASS

NO ACCUMULATED TOLERANCE

CIRCUIT No.1
(BASIS PIN)

±0.15
2.45
±0.1
F
3.05
±0.15
1.2


TYP 1.8 MIN
PITCH
2


±0.1
1.2
±0.1
2.4

TYP 3.3 MIN

3

RECOMENOE P.C.BOARD LAYOUT
(P.C.B THK:0.8mm MIN)



THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC $\pm$ -
	1 PLC $\pm$ -
	2 PLC $\pm$ -
	3 PLC $\pm$ -
	4 PLC $\pm$ -
	ANGLES $\pm$ -
MATERIAL	FINISH
SEE NOTE	SEE NOTE

DWN	—
CHK	—
APVD	—
PRODUCT SPEC	
108-60016	
APPLICATION SPEC	
WEIGHT 0	
CUSTOMER DRAWING	

ON TAPING (EMBOSS)
SMT TYPE POST HDR ASS'Y(V)
W/O BOSS &WITH TAIL TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
A3	00779	C-292175	—		
		SCALE	N/A	SHEET	3 OF 3
				REV	B4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-292175-7](#)