





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R	HOUSING RESIN CHANGED	27OCT2021	SCB	KJK

SEE SHEET 2
FOR P/N'S -51 THRU -90



98-4	2	88.9 [3.500]	91.44 [3.600]	72	3-534998-6
	2	86.36 [3.400]	88.90 [3.500]	70	3-534998-5
		83.82 [3.300]	86.36 [3.400]	68	3-534998-4
	2	81.28 [3.200]	83.82 [3.300]	66	3-534998-3
	2	78.74 [3.100]	81.28 [3.200]	64	3-534998-2
	2	76.20 [3.000]	78.74 [3.100]	62	3-534998-1
	2	73.66 [2.900]	76.20 [3.000]	60	3-534998-0
	2	71.12 [2.800]	73.66 [2.900]	58	2-534998-9
	2	68.58 [2.700]	71.12 [2.800]	56	2-534998-8
	2	66.04 [2.600]	68.58 [2.700]	54	2-534998-7
98-6		63.50 [2.500]	66.04 [2.600]	52	2-534998-6
	2	60.96 [2.400]	63.50 [2.500]	50	2-534998-5
	2	58.42 [2.300]	60.96 [2.400]	48	2-534998-4
	2	55.88 [2.200]	58.42 [2.300]	46	2-534998-3
	2	53.34 [2.100]	55.88 [2.200]	44	2-534998-2
	2	50.80 [2.000]	53.34 [2.100]	42	2-534998-1
	2	48.26 [1.900]	50.80 [2.000]	40	2-534998-0
	2	45.72 [1.800]	48.26 [1.900]	38	1-534998-9
	2	43.18 [1.700]	45.72 [1.800]	36	1-534998-8
	2	40.64 [1.600]	43.18 [1.700]	34	1-534998-7
	2	38.10 [1.500]	40.64 [1.600]	32	1-534998-6
	2	35.56 [1.400]	38.10 [1.500]	30	1-534998-5
	2	33.02 [1.300]	35.56 [1.400]	28	1-534998-4
	2	30.48 [1.200]	33.02 [1.300]	26	1-534998-3
	2	27.94 [1.100]	30.48 [1.200]	24	1-534998-2
	2	25.40 [1.000]	27.94 [1.100]	22	1-534998-1
	2	22.86 [.900]	25.40 [1.000]	20	1-534998-0
	2	20.32 [.800]	22.86 [.900]	18	534998-9
	2	17.78 [.700]	20.32 [.800]	16	534998-8
	2	15.24 [.600]	17.78 [.700]	14	534998-7
2	12.70 [.500]	15.24 [.600]	12	534998-6	
2 10	10.16 [.400]	12.70 [.500]	10	534998-5	
2 10	7.62 [.300]	10.16 [.400]	8	534998-4	
2 10	5.08 [.200]	7.62 [.300]	6	534998-3	
2 10	2.54 [.100]	5.08 [.200]	4	534998-2	
2 10	-	2.54 [.100]	2	6 534998-1	
	B	A	NO OF POSN	PART NUMBER	

- | | |
|----|---|
| 1 | HOUSING: FLAME RETARDANT, GLASS FILLED, THERMOPLASTIC, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE |
| 2 | CONTACT: DUPLEX PLATED 0.76μm[.000030] GOLD IN CONTACT AREA, 3.81–7.62μm[.000150–.000300] BRIGHT TIN–LEAD ON LEADS, ALL OVER 1.27μm[.000050] NICKEL |
| 3 | THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY – NOT TO CONTACT LOCATIONS |
| 4 | PART NUMBER AND DATE CODE ARE MARKED IN APPROXIMATE LOCATION SHOWN,EITHER SIDE. |
| 5 | TOLERANCE IS NON–CUMULATIVE. |
| 6 | 2 POSITION DATE CODE IS MARKED OPPOSITE SIDE OF TE CONNECTIVITY LOGO. |
| 7 | POINT–OF–MEASUREMENT DIMENSION FOR PLATING THICKNESS (INSIDE CONTACT BEAM). |
| 8 | POINT–OF–CONTACT DIMENSION. |
| 9 | TE CONNECTIVITY TRADEMARK AND CSA LOGO ARE MOLDED INTO HOUSING, THIS LOCATION. |
| 10 | NO PART NUMBER MARKING REQUIRED FOR THIS PART. |
| 11 | CONTACT: DUPLEX PLATED 0.76μm[.000030] GOLD IN CONTACT AREA, 3.81–7.62μm[.000150–.000300] MATTE TIN ON LEADS, ALL OVER 1.27μm[.000050] NICKEL |
| 12 | ROHS 2002/95/EC COMPLIANT |

2	SUPERCEDED BY 9-534998-0	99.06 [3.900]	101.60 [4.000]	80	4-534998-0
		96.52 [3.800]	99.06 [3.900]	78	3-534998-9
	2	93.98 [3.700]	96.52 [3.800]	76	3-534998-8
	2	91.44 [3.600]	93.98 [3.700]	74	3-534998-7
		B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BINNER	06NOV02	 TE Connectivity Ltd.
		CHK J. OLSON	06NOV02	
		APV J. OLSON	06NOV02	
		NAME		
DIMENSIONS: mm (INCHES)		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLOC ± 1 PLOC ± 2 PLOC ± 0.13 (0.005) 3 PLOC ± 4 PLOC ± ANGLES ± FINISH		RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU
MATERIAL: 		PRODUCT SPEC: 108-25022		
		APPLICATION SPEC: 114-25018		
		WEIGHT: —		
		SIZE CASE CODE DRAWING NO A1 00779 C=534998		RESTRICTED TO: —
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 2
				REV R

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-534998-2](#)