

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS







P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	05MAR2015	DW	CW
	B	ECR-15-015267	22OCT2015	DW	CW
	C	ECR-21-111798	03SEP2021	WQR	CW

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 400V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: $-40^{\circ}C \sim +125^{\circ}C$
WIRE RANGE: $0.14mm^2 \sim 4mm^2$ (AWG26-AWG12)
CONTACT TYPE: CRIMP CONTACT
- CONTACTS NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20300X10XX000)

注释:


- 技术参数:
绝缘材料: PC
额定电压: 400V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 6KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: $-40^{\circ}C \sim +125^{\circ}C$
接线范围: $0.14mm^2 \sim 4mm^2$ (AWG26-AWG12)
接线类型: 冷压接
- 端子需要单独订购,
(订货号参考图面: T20300X10XX000)

4X M3 THREAD, RECOMMENDED
TIGHTENING TORQUE 0.5NmPANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±0.1
1 PLC	±0.15
2 PLC	±0.2
3 PLC	±0.25
4 PLC	±0.3
ANGLES	±0.5

FINISH

DWN 05MAR2015

David Wang

CHK 05MAR2015

Chris Wang

APVD 05MAR2015

Xiang Xu

PRODUCT SPEC

108-137068

APPLICATION SPEC

114-137068

WEIGHT

-

Customer Drawing

HEEE-072-M

T2050722101-000

DESCRIPTION

PART NUMBER

TE Connectivity

NAME

HEEE-072-M

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C

T2050722101000

-

SCALE

1:1

SHEET

1 OF 1

REV

C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2050722101-000](#)