

SPECIFICATION CONTROL DRAWING

SCD


82A1141

Title FOUR CONDUCTOR CABLE, SHIELDED, JACKETED,
GENERAL PURPOSE, FLEXIBLE, 600 VOLT

Date 6-1-16

Revision D

This specification sheet forms a part of the latest issue of Raychem Specification 80.



CABLE CONSTRUCTION DETAILS

PART NUMBER ^{1/}	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inch)		OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
82A1141-28-*	28	38	.005	.008	.103	.118	10.1
82A1141-26-*	26	38	.006	.009	.115	.132	12.8
82A1141-24-*	24	38	.006	.009	.125	.144	16.4
82A1141-22-*	22	38	.007	.010	.141	.163	21.2
82A1141-20-*	20	38	.007	.011	.167	.194	28.9
82A1141-18-*	18	38	.008	.012	.196	.228	41.8
82A1141-16-*	16	38	.009	.013	.234	.273	59.8
82A1141-14-*	14	38	.010	.015	.287	.335	91.5
82A1141-12-*	12	36	.012	.018	.350	.409	138.
82A1141-10-*	10	36	.014	.021	.443	.519	223.
82A1141-8-*	8	34	.017	.025	.548	.643	347.
82A1141-6-*	6	34	.019	.029	.655	.770	515.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C
 Maximum continuous conductor temperature
 VOLTAGE RATING: 600 volts (rms) at sea level
 CROSSLINKING PROOF TEST: 300 ± 3°C for 7 hours
 DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz
 JACKET COLOR: White preferred
 JACKET ELONGATION AND TENSILE STRENGTH:
 Elongation, 100% (minimum)
 Tensile Strength, 3000 lbf/in² (minimum)
 JACKET FLAWS:
 Spark Test, 1500 volts (rms)
 Impulse Dielectric Test, 6.0 kV (peak)
 SECANT MODULUS (Test per ASTM D 882):
 4.0 x 10⁴ lbf/in² (maximum),
 2% strain, 2 inch jaw separation, 0.2 inch/minute

SHIELD COVERAGE: 85% (minimum)
 VOLTAGE WITHSTAND (Post Environmental):
 1000 volts (rms), 60 Hz, 1 minute

^{1/} PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color. Colors shown do not necessarily reflect the sequence of manufacturing.
 Example: AWG 20, orange, green, blue, and white component wires; white jacket:
 82A1141-20-3/5/6/9-9

NOTE: Nominal values are for information only. Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

^{1/} COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[82A1141-16-MST4-9CS3022](#)