

TERMINAL, T-N R 1/0 1/2 ✓ ACTIVE

TERMINYL

TE Part # 324058

TE Internal #: 324058

Mil-Spec: [MS25036-134]

[View on TE.com >](#)



Terminals & Splices > Rings & Spades



Wire Size: 83700 – 119500 CMA

Stud Size: 1/2, M12

Stud Diameter: 13.08 mm [.5 in]

Features

Product Type Features

Shape Description	RING-047
Stud Size	1/2, M12
Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Inspection Slot	No
Insulation Sleeve Color	Blue
Weight per Piece	25.121 g
Plating Material	Copper, Tin

Contact Features

Military Part Class	Class II
Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Wire Size	83700 – 119500 CMA
Stud Diameter	13.08 mm[.5 in]
Tongue Thickness	1.85 mm[.073 in]
Overall Length	62.33 mm[2.4539 in]

Usage Conditions

Operating Temperature Range	105 °C
-----------------------------	--------

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	Yes
----------------------	-----

Packaging Features

Packaging Quantity	50
Packaging Method	Loose Piece

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in

articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1490700-1
 DIE ASSEMBLY,TERMINYL
 1/0



TE Part # 47824
 DIE TERMINYL 69066 1/0

Customers Also Bought



TE Part #324057
 TERMINAL,T-N R 1/0 3/8



TE Part #177103-000
 44AM1131-16-MST3-
 9CS2275



TE Part #158631-000
 44AM1131-20-MST3-
 9CS2275




TE Part #324055
 TERMINAL,T-N R 2 1/2



TE Part #324056
 TERMINAL,T-N R 1/0 1/4




TE Part #819117-000
 202F232-51-0



TE Part #819118-000
 202F242-51-0



TE Part #819103-000
 462A421-51-0



TE Part #290139-000
 202E336-51/164-0



TE Part #970677N002
 S02-01-RCS453

Documents

Product Drawings

TERMINAL,T-N R 1/0 1/2

TE Part # 324058
TE Internal #: 324058
Mil-Spec: [MS25036-134]



TERMINAL,T-N R 1/0 1/2

English

CAD Files

Customer View Model

[ENG_CVM_324058_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_324058_G.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_324058_G.2d_dxf.zip](#)

English

3D PDF

English

Agency Approvals

[UL Report](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[MS25036-134](#)