

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E1	REVISED PER ECO-15-009619	17JUL2015	AP	PS


NOTES:

MATERIAL:
 HOUSING: THERMOPLASTIC, UL94V-0, BLACK.
 TERMINAL: BRIGHT TIN PLATED, COPPER ALLOY.
 SCREWS: ZINC PLATED STEEL.

ELECTRICAL:
 RATED CURRENT: 10A.
 OPERATING VOLTAGE: 300V.
 WIRE RANGE: 16-30 AWG.

MECHANICAL:
 PITCH (TERMINAL SPACING): .250"
 OPERATING TEMP.: 120°C MAX.

1 M3 SCREWS BOTTOMED.



DIM "A" IN INCH	NO. OF POS.	CATALOG NUMBER	TE PART NO.
7.25	28	3PCR-28-008	2-1546525-8
7.00	27	3PCR-27-008	2-1546525-7
6.75	26	3PCR-26-008	2-1546525-6
6.50	25	3PCR-25-008	2-1546525-5
6.25	24	3PCR-24-008	2-1546525-4
6.00	23	3PCR-23-008	2-1546525-3
5.75	22	3PCR-22-008	2-1546525-2
5.50	21	3PCR-21-008	2-1546525-1
5.25	20	3PCR-20-008	2-1546525-0
5.00	19	3PCR-19-008	1-1546525-9
4.75	18	3PCR-18-008	1-1546525-8
4.50	17	3PCR-17-008	1-1546525-7
4.25	16	3PCR-16-008	1-1546525-6
4.00	15	3PCR-15-008	1-1546525-5
3.75	14	3PCR-14-008	1-1546525-4
3.50	13	3PCR-13-008	1-1546525-3
3.25	12	3PCR-12-008	1-1546119-8
3.00	11	3PCR-11-008	1-1546525-1
2.75	10	3PCR-10-008	1-1546525-0
2.50	9	3PCR-09-008	1546525-9
2.25	8	3PCR-08-008	1546525-8
2.00	7	3PCR-07-008	1-1546119-1
1.75	6	3PCR-06-008	1546525-6
1.50	5	3PCR-05-303	2-1546525-9
1.50	5	3PCR-05-008	1546119-9
1.25	4	3PCR-04-008	1546525-4
1.00	3	3PCR-03-008	1546119-7
0.75	2	3PCR-02-008	1546525-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 4/17/03	STE TE Connectivity	
DIMENSIONS: INCHES		CHK S. YODER 4/17/03		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. YODER 4/17/03	NAME	
0 PLC ± -		PRODUCT SPEC	3PCR-XX-008 ASSEMBLY	
1 PLC ± -		APPLICATION SPEC	SIZE	CAGE CODE
2 PLC ± .02		WEIGHT -	A3	00779
3 PLC ± .010		CUSTOMER DRAWING	DRAWING NO C-1546119-7	
4 PLC ± -		SCALE NTS	RESTRICTED TO	
ANGLES ± 1°		SHEET 1 OF 1	REV E1	
MATERIAL -	FINISH -			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3PCR-02-008](#)