

V23100V6002A101 ✓ ACTIVE

Axicom | Axicom Reed Relay V23100 -V4

TE Internal #: 1393803-4

Axicom Reed Relay V23100 -V4, Power Relays, Standard, 130mW
Coil Power Rating DC, 1100Ω Coil Resistance, 12VDC Coil Voltage
Rating

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Power Relays



Power Relay Type: **Standard**

Coil Power Rating DC: **130 mW**

Coil Resistance: **1100 Ω**

Coil Voltage Rating: **12 VDC**

Contact Arrangement: **1 Form A (NO)**

Features

Product Type Features

| | |
|------------------|----------|
| Power Relay Type | Standard |
|------------------|----------|

Electrical Characteristics

| | |
|---------------------------------|---------|
| Coil Power Rating DC | 130 mW |
| Coil Resistance | 1100 Ω |
| Coil Voltage Rating | 12 VDC |
| Contact Switching Voltage (Max) | 100 VDC |
| Contact Voltage Rating | 100 VDC |

Contact Features

| | |
|------------------------------|---------------|
| Contact Arrangement | 1 Form A (NO) |
| Contact Current Rating (Max) | .75 A |
| Contact Number of Poles | 2 |
| Relay Terminal Type | PCB-THT |

Mechanical Attachment

| | |
|---------------------|-----------------------|
| Relay Mounting Type | Printed Circuit Board |
|---------------------|-----------------------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
|------------------------------|-----------|



| | |
|---|---|
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Wave solder capable to 265°C |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Axicom Reed Relay V23100 -V4



Customers Also Bought



TE Part #DTT-20-03
CRIMP TOOL



TE Part #K1007153
Toggle Switch 08-1-1-13



TE Part #K1060489
Relay 29-113-12



TE Part #DRC16-70SBE-P013UK
PLG, 70P, BLK, E, SEAL BOND, B



TE Part #YHDP26-24-35PEL017
PLG, 35P, BLK, E, RNG, 16/20, P



TE Part #834936-000
MWTM-10/3-100/S(S100)



TE Part #K1002956
Toggle Switch 08-4-1-13



TE Part #K1008699
Relay 26-60-05



TE Part #HDP24-24-16SE-L015
REC, 16P, BLK, E, THD, 12, S



TE Part #SRK-PC-080-25-601
PIN, SOLID, SIZE M8, 25mm2, AG

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1393803-4_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1393803-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1393803-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Reed Relay V23100-V6](#)

English

V23100V6002A101

Axicom Reed Relay V23100 -V4, Power Relays, Standard, 130mW Coil Power Rating
DC, 1100Ω Coil Resistance, 12VDC Coil Voltage Rating



Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1393803-4](#)