

# KHU-17A18-120 ✓ ACTIVE

Potter & Brumfield | Potter & Brumfield KHA


TE Internal #: 3-1393123-7

Potter & Brumfield KHA, Power Relays, Industrial Panel Plug-In, Monostable, AC, 1 – 2VA Coil Power Rating Class, 1.35VA Coil Power Rating AC

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Power Relays



Power Relay Type: **Industrial Panel Plug-In**

Coil Magnetic System: **Monostable, AC**

Coil Power Rating Class: **[ 1 – 2 VA ]**

Coil Power Rating AC: **1.35 VA**

Coil Resistance: **3900 Ω**

## Features

### Product Type Features

Power Relay Type	Industrial Panel Plug-In
------------------	--------------------------

### Electrical Characteristics

Insulation Initial Dielectric Between Coil & Contact Class	1000 – 1500 V
Insulation Initial Dielectric Between Contacts & Coil	1500 Vrms
Actuating System	AC
Insulation Initial Dielectric Between Open Contacts	1000 Vrms
Insulation Initial Dielectric Between Adjacent Contacts	1500 Vrms
Insulation Initial Resistance	100 MΩ
Coil Magnetic System	Monostable, AC
	1 – 2 VA
Coil Power Rating AC	1.35 VA
Coil Resistance	3900 Ω
Coil Special Features	UL Coil Insulation Class B
Coil Voltage Rating	120 VAC
Contact Switching Load (Min)	50mA @ 12V
Contact Voltage Rating	240 VAC

### Body Features

Product Weight	45 g[1.587 oz]
----------------	----------------



### Contact Features

Contact Plating Material	Gold
Contact Arrangement	4 Form C (CO)
Contact Current Class	2 – 5 A, 16 A
Contact Current Rating (Max)	2.5 A
Contact Material	Ag
Contact Number of Poles	4
Terminal Type	Plug-In, Solder

### Mechanical Attachment

Relay Mounting Type	Socket
---------------------	--------

### Dimensions

Length Class (Mechanical)	25 – 30 mm
Height Class (Mechanical)	30 – 40 mm
Width Class (Mechanical)	20 – 25 mm
Product Width	21.8 mm[.858 in]
Product Length	28.2 mm[1.111 in]
Product Height	38.1 mm[1.5 in]

### Usage Conditions

Environmental Ambient Temperature Class	50 – 70 °C
Environmental Ambient Temperature (Max)	70 °C[158 °F]
Operating Temperature Range	-45 – 70 °C

### Packaging Features

Packaging Method	Package
------------------	---------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC



Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 1419106-2  
27E007=SOCKET,KH,14,PC,PHEN,BL



TE Part # 1419106-3  
27E023=SOCKET,KH,14,PC,PHEN,BL



TE Part # 1419106-1  
27E006=SOCKET,KH,14,SLG,G/T,PH




TE Part # 1-1393143-9  
27E166=SOCKET,KH,14,SCW,PLES




TE Part # 2-1419106-6  
27E894=SOCKET,KH,14,SCW,POLY,N

### Also in the Series | Potter & Brumfield KHA



Power Relays(80)



Relay Accessories, Sockets & Clips(7)

### Customers Also Bought



TE Part #326859  
TERMINAL,PIDG SPD 12-10 6



TE Part #T4111502041-000  
M12,MALE,STRAIGHT,D CODE,4P,  
PG9,GOLD



TE Part #2-1393122-0  
KHAU-17A11-120=KH



TE Part #102241-2  
04 MODIV HG COMP SR .100 POL



TE Part #3-1393766-8  
R10-E1Y2-S800=R10



TE Part #1437471-2  
SSC12APA=120V 60HZ .1 TO 10 SE



TE Part #3-1393766-2  
R10-E1Y2-JJ5.0K=R10

## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_3-1393123-7\\_C.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_3-1393123-7\\_C.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_3-1393123-7\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[KHA General Purpose Dry Circuit to 5A Multicontact AC or DC Relay](#)

English

[Industrial Relays Quick Reference Guide](#)

English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)

### Product Specifications

[Definitions, Handling, Processing, Testing and Use of Relays](#)

English



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[KHU-17A18-120](#)