



REVISIONS ÄNDERUNGEN DESCRIPTION BESCHREIBUNG				
P	LTR	DATE	DWN	APVD
	E1	NOTE 1 0.76µm PLATING UPDATE (PdNi+AuFLASH)	14JUL2023	BGC PS




NOTES:

- 1 MIN. 3.0–5.0µm Sn OVER 1.27µm Ni
- 2 MATING SIDE: Min 0.76µm (PdNi + Au FLASH) IN ZONE "F" OVER Min 1.27µm Ni
(Alternative plating – Min 0.76µm Au OVER Min 1.27µm Ni)
- 3 NO BURRS PERMITTED
- 4 PARTS WITHOUT BURRS AND SHAVINGS

0 – –4As shown

1241126-4	△ △	CuSn	CONTACT PIN	2
	BLACK	PBT	HOUSING	1
PART NO.	FINISH/COLOR	MATERIAL	DESCRIPTION	ITEM NO.

DIMENSIONS: MASSENHEITEN mm		DWN A. Zitz 24JAN1998	MATERIAL SEE TABLE		FINISH OBERFLAECH/FARBE SEE TABLE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN A. ISO 8015 0 PLC ± 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES / WINKEL ± -		CHK U. Laudenbach 24JUN1998	TE Connectivity			
		APVD —				
		PRODUCT SPEC PRODUKTSPEZ. 108-18012	NAME AMPMODU II PIN HEADER, DUAL ROW			
		APPLICATION SPEC VERARBEITUNGSSPEZ. —				
		WEIGHT GEWICHT —	SIZE A4	CAGE CODE 00779	DRAWING NO ZEICHNUNGS-NR. C-1241126	RESTRICTED TO NUR FUER —
		CUSTOMER DRAWING / KUNDENZEICHNUNG				SCALE MASSSTAB 5:1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1241126-4](#)