



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B3	ECO-13-000550	10JAN2013	DS	AT
	B3	ECO-14-000116	27FEB2014	DS	AT
	B4	ECN-21-124299	28OCT2021	SS	PK
	B5	ECN-24-265836	13MAY2024	SS	PK



- 1

MATERIAL 1:
TYPE: COPPER ALLOY
- 2

MATERIAL 2:
TYPE: ALTERNATE COPPER ALLOY, NO ANNEALING
- 3

FINISH:
UNDERPLATE TYPE: NICKEL
TOP PLATE TYPE: TIN
- 4

PARTS MUST BE FREE OF BURRS, CRACKS, OR OTHER
VISUAL IMPERFECTIONS THAT MAY AFFECT FIT FORM OR FUNCTION
- 5

NOTE DELETED
- 6

NOTE DELETED

	5.41	6.10	7.70	SIZE C	1-1587829-3
	5.41	6.10	7.70	SIZE C	1587829-3
	4.76	5.41	7.00	SIZE B	1-1587829-2
	4.76	5.41	7.00	SIZE B	1587829-2
	4.11	4.76	6.40	SIZE A	1-1587829-1
	4.11	4.76	6.40	SIZE A	1587829-1
<i>MIN</i>		<i>MAX</i>	E	<i>DESCRIPTION</i>	<i>PART NO</i>
<i>WIRE O.D.</i>					

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D SIMPSON 01JUN2009	TE Connectivity			
		CHK A TYLER 01JUN2009				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME OUTER FERRULE, HVA280 -			
	0 PLC ± 1 PLC ±0.2 2 PLC ±0.10 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±	PRODUCT SPEC 108-2394				
MATERIAL	FINISH	APPLICATION SPEC 114-13259	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
- 2 1	- 3	WEIGHT -	A3	00779	C-1587829	-
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV B5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1587829-1](#)