




| LOC | DIST | REVISIONS | | | | |
|-----|------|-----------|-----|--------------------------|-----------|----------|
| | | P | LTR | DESCRIPTION | DATE | DWN APVD |
| — | — | | B | UPDATE PER ECO-11-013272 | 28 JUN 11 | CAS MKS |

SUGGESTED PANEL CUT-OUT

2X R.063






WIRE LENGTH SPECIFIED IN NANONICS PART NUMBER



M8.0 X 0.75-6g THREAD

.469
HEX FLANGE
AND JAM NUT



- 1
- 2
- 3
- 4
- CONNECTOR BODY & JAM NUT MATERIAL: 303 STAINLESS STEEL, PASSIVATED PER SAE-AMS-2700
INSULATOR MATERIAL: LIQUID CRYSTAL POLYMER (LCP) PER ASTM D5138 OR POLYPHENYLENE SULFIDE (PPS) PER ASTM D4067
O-RING MATERIAL: FLUOROSILICONE
WIRE TERMINATION: 28 AWG SOLID, 30 AWG STRANDED WIRE OR SMALLER
LUBRICATE O-RING WITH PARKER SUPER-O-LUBE PRIOR TO INSTALLATION
THIS DRAWING ALSO IDENTIFIED AS NANONICS 303-0183

| | | | | | | |
|--|--|------------------------------|--|--|-------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN C SCHOLL 21 JAN 10 | TE Connectivity | | | |
| DIMENSIONS: INCHES | | CHK M STORRY 21 JAN 10 | | | | |
| | | APVD — | NAME RECEPTACLE ASSEMBLY, CIRCULAR, PANEL MOUNT, THREADED COUPLING / QUICK DISCONNECT, STAINLESS STEEL SHELL, 19 POSITION | | | |
| | | PRODUCT SPEC — | SIZE A2 | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APPLICATION SPEC — | CAGE CODE 0PJN9 | | DRAWING NO C=1925133 | |
| MATERIAL SEE NOTES | | WEIGHT — | RESTRICTED TO — | | SCALE 6:1 | |
| FINISH SEE NOTES | | CUSTOMER DRAWING | SHEET 1 of 1 | | REV B | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1925133-2](#)