



P	LTR	DESCRIPTION	DATE	DWN	APVD
B2		REVISED PER ECO-16-006284	25APR2016	ERL	ERL
C		REVISED PER ECO-16-009531	27JUN2016	JAB	ERL
C1		REVISED PER ECO-20-000275	27JAN2020	KP	MB
C2		REVISED PER ECO-20-008977	26JUN2020	JMS	MB


D



ISOMETRIC VIEWS
SCALE 6:1

D

C



C

B

- 1 NOSE CONE - NYLON WITH INCREASED WELDLINE STRENGTH, COLOR: SEE TABLE, 30% GLASS FILLED. DIELECTRIC - POLYESTER PCT, NATURAL, 30% GLASS FILLED. PIN CONTACT - BRASS. OUTER SHELL - ZINC.
- 2 PIN CONTACT - 0.38µm MIN GOLD ON INTERFACE END, 2.5µm MIN TIN ON SOLDER END, BOTH OVER 1.3µm MIN NICKEL. OUTER SHELL - 2.0µm MIN TIN OVER 1.52µm MIN NICKEL, BOTH OVER 2.54µm MIN COPPER.
- 3 REMOVED
- 4 MASS = 1.05g.
- 5 MINIMUM RECOMMENDED GROUND PLANE.
- 6 SIGNAL DIMENSION TRACE RECOMMENDED FOR OPTIMUM SIGNAL PERFORMANCE.
- 7 MALE INTERFACE PER ISO-20860-1, ROAD VEHICLES 50 Ohm RADIO FREQUENCY INTERFACE.
- 8 REELING VIEW FOR REFERENCE ONLY TO SHOW UNREELING DIRECTION

B

A


2	TAPE AND REEL	PER DETAIL Z	WATER BLUE	Z	7-2203452-0
		PER DETAIL N	PASTEL GREEN	N	6-2203452-3
		PER DETAIL M	PASTEL ORANGE	M	6-2203452-2
		PER DETAIL L	CARMINE RED	L	6-2203452-1
		PER DETAIL K	CURRY	K	6-2203452-0
		PER DETAIL I	BEIGE	I	5-2203452-9
		PER DETAIL H	HEATHER VIOLET	H	5-2203452-8
		PER DETAIL G	BLUE GREY	G	5-2203452-7
		PER DETAIL F	NUT BROWN	F	5-2203452-6
		PER DETAIL E	LEAF GREEN	E	5-2203452-5
		PER DETAIL D	CLARET VIOLET	D	5-2203452-4
		PER DETAIL C	SIGNAL BLUE	C	5-2203452-3
		PER DETAIL B	CREAM	B	5-2203452-2
		PER DETAIL A	JET BLACK	A	5-2203452-1
		PER DETAIL Z	WATER BLUE	Z	2-2203452-0
		PER DETAIL N	PASTEL GREEN	N	1-2203452-3
		PER DETAIL M	PASTEL ORANGE	M	1-2203452-2
2	TRAY	PER DETAIL L	CARMINE RED	L	1-2203452-1
		PER DETAIL K	CURRY	K	1-2203452-0
		PER DETAIL I	BEIGE	I	2203452-9
		PER DETAIL H	HEATHER VIOLET	H	2203452-8
		PER DETAIL G	BLUE GREY	G	2203452-7
		PER DETAIL F	NUT BROWN	F	2203452-6
		PER DETAIL E	LEAF GREEN	E	2203452-5
		PER DETAIL D	CLARET VIOLET	D	2203452-4
		PER DETAIL C	SIGNAL BLUE	C	2203452-3
		PER DETAIL B	CREAM	B	2203452-2
		PER DETAIL A	JET BLACK	A	2203452-1
FINISH	PACKAGING	KEYING	NOSE CONE COLOR	KEYING CODE	PART NUMBER

A


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. FERNANDES 5MAY2013	TE Connectivity
DIMENSIONS: mm		CHK R. J. DEMARCHIS 5MAY2013	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. J. DEMARCHIS 5MAY2013	
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±-		PRODUCT SPEC 108-32058 APPLICATION SPEC 114-32108	
MATERIAL 1	SEE TABLE	WEIGHT 4	NAME MALE ASSEMBLY, 1 POSITION, VERTICAL, PCB, FAKRA
CUSTOMER DRAWING		SIZE 114-32108	RESTRICTED TO -
		CAGE CODE 114-32108	SCALE 8:1
		DRAWING NO. 114-32108	SHEET 1 OF 2
		REV C2	

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-


CODINGS




DETAIL A
SCALE 5:1




DETAIL B
SCALE 5:1




DETAIL C
SCALE 5:1




DETAIL D
SCALE 5:1




DETAIL E
SCALE 5:1




DETAIL F
SCALE 5:1




DETAIL G
SCALE 5:1




DETAIL H
SCALE 5:1




DETAIL I
SCALE 5:1




DETAIL K
SCALE 5:1




DETAIL L
SCALE 5:1







DETAIL M
SCALE 5:1




DETAIL N
SCALE 5:1



DETAIL Z
SCALE 5:1



8 DIRECTION OF UNREELING



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: R. FERNANDES CHK: R. J. DEMARCHIS APVD: R. J. DEMARCHIS	15MAY2013 15MAY2013 15MAY2013	TE TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME: MALE ASSEMBLY, 1 POSITION, VERTICAL, PCB, FAKRA	
mm		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		SIZE: 108-32058 APPLICATION SPEC: 114-32108	
MATERIAL: -		SEE TABLE		WEIGHT: 4	
-		-		CUSTOMER DRAWING	
SCALE: 8:1		SHEET: 2 OF 2		REV: C2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-2203452-1](#)