





LOC	DIST	REVISIONS					
IN	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C1	ECO-20-000275	27JAN2020	KP	MB

- 1
- NOSE CONE - NYLON, COLOR: SEE TABLE, 25% GLASS FILLED.
DIELECTRIC - POLYESTER PCT, NATURAL, 30% GLASS FILLED.
PIN CONTACT - BRASS.
OUTER SHELL - ZINC.
- 2
- PIN CONTACT - 0.38µm MIN GOLD ON INTERFACE END, 2.5µm MIN TIN ON SOLDER END,
BOTH OVER 1.3µm MIN NICKEL.
OUTER SHELL - 2.0µm MIN TIN OVER 1.52µm MIN NICKEL,
BOTH OVER 2.54µm MIN COPPER.
- 3
- REMOVED
- 4
- MINIMUM SIGNAL PAD FOR SOLDER.
- 5
- MINIMUM RECOMMENDED GROUND PLANE.
- 6
- SIGNAL DIMENSION TRACE RECOMMENDED FOR
OPTIMUM SIGNAL PERFORMANCE.
- 7
- MALE INTERFACE PER ISO-20860-1, ROAD VEHICLES 50 Ohm RADIO FREQUENCY INTERFACE.
- 8
- REELING VIEW FOR REFERENCE ONLY TO SHOW UNREELING DIRECTION



ISOMETRIC VIEWS
SCALE 6:1




8 DIRECTION OF UNREELING


2	TAPE AND REEL	PER DETAIL Z	WATER BLUE	Z	7-2272788-0
		PER DETAIL N	PASTEL GREEN	N	6-2272788-3
		PER DETAIL M	PASTEL ORANGE	M	6-2272788-2
		PER DETAIL L	CARMINE RED	L	6-2272788-1
		PER DETAIL K	CURRY	K	6-2272788-0
		PER DETAIL I	BEIGE	I	5-2272788-9
		PER DETAIL H	HEATHER VIOLE	H	5-2272788-8
		PER DETAIL G	BLUE GREY	G	5-2272788-7
		PER DETAIL F	NUT BROWN	F	5-2272788-6
		PER DETAIL E	LEAF GREEN	E	5-2272788-5
		PER DETAIL D	CLARET VIOLET	D	5-2272788-4
		PER DETAIL C	SIGNAL BLUE	C	5-2272788-3
		PER DETAIL B	CREAM	B	5-2272788-2
		PER DETAIL A	JET BLACK	A	5-2272788-1
2	TRAY	PER DETAIL Z	WATER BLUE	Z	2-2272788-0
		PER DETAIL N	PASTEL GREEN	N	1-2272788-3
		PER DETAIL M	PASTEL ORANGE	M	1-2272788-2
		PER DETAIL L	CARMINE RED	L	1-2272788-1
		PER DETAIL K	CURRY	K	1-2272788-0
		PER DETAIL I	BEIGE	I	2272788-9
		PER DETAIL H	HEATHER VIOLE	H	2272788-8
		PER DETAIL G	BLUE GREY	G	2272788-7
		PER DETAIL F	NUT BROWN	F	2272788-6
		PER DETAIL E	LEAF GREEN	E	2272788-5
		PER DETAIL D	CLARET VIOLET	D	2272788-4
		PER DETAIL C	SIGNAL BLUE	C	2272788-3
		PER DETAIL B	CREAM	B	2272788-2
		PER DETAIL A	JET BLACK	A	2272788-1
FINISH	PACKAGING	CODING	NOSE CONE COLOR	CODING REF	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. PETERSON 30MAY2014	TE Connectivity				
DIMENSIONS:		CHK D. J. LANE 30MAY2014	NAME				
mm		APVD D. J. LANE 30MAY2014	PRODUCT SPEC				
			108-32058				
			APPLICATION SPEC				
			114-32108				
MATERIAL		FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
1		SEE TABLE	2.03g	A1	00779	C=2272788	-
		CUSTOMER DRAWING	SCALE	8:1	SHEET	1 OF 2	REV C1


LOC		DIST		REVISIONS				
1N		00		P.	LYR	DESCRIPTION		DATE
				-		SEE SHEET 1		-




DETAIL A
SCALE 5:1




DETAIL B
SCALE 5:1




DETAIL C
SCALE 5:1




DETAIL D
SCALE 5:1




DETAIL E
SCALE 5:1




DETAIL F
SCALE 5:1




DETAIL G
SCALE 5:1




DETAIL H
SCALE 5:1




DETAIL I
SCALE 5:1




DETAIL K
SCALE 5:1




DETAIL L
SCALE 5:1





DETAIL M
SCALE 5:1



DETAIL N
SCALE 5:1



DETAIL Z
SCALE 5:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. PETERSON 30MAY2014	TE Connectivity	
DIMENSIONS:		CHK D. J. LANE 30MAY2014		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. J. LANE 30MAY2014	NAME	
	0 PLC	±	PRODUCT SPEC	
	1 PLC	±0.2	108-32058	
	2 PLC	±0.08	APPLICATION SPEC	
	3 PLC	±	114-32108	
MATERIAL	ANGLES	±	WEIGHT	
	FINISH	±	2.03g	
SEE TABLE		CUSTOMER DRAWING		
		SCALE		8:1
		SHEET		2 OF 2
		REV		C1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-2272788-0](#)