



BOARD-TO-BOARD HEADERS & RECEPTACLES



TE CONNECTIVITY (TE) 02 MODII HORZ SR CE 100CL AMPMODU | AMPMODU

535676-1
TE Internal Number: 535676-1

Not EU RoHS or ELV Compliant
[Find Compliant Alternatives](#)

Connector Style **Receptacle**

Centerline **2.54 mm [.1 in]**

Number of Positions **2**

Packaging Method **Tube, Tube/Box**

Contact Mating Area Plating Material **Gold**

Active

[PRODUCT DRAWING](#)
English

[3D PDF](#)

Product Drawings

[AMPMODU MOD II RECEPTACLE ASSEMBLY, HORIZONTAL, .100 CL, SINGLE ROW, CLOSED-ENTRY, SHORT POINT OF CONTACT, END-TO-END STACKABLE](#)
PDF
English

CAD Files

[Customer View Model](#)
3D_IGS.ZIP
English

[Customer View Model](#)
2D_DXF.ZIP
English

[3D PDF](#)
PDF
English

[Customer View Model](#)
3D_STP.ZIP
English

Product Specifications

Product Specification [AMPMODU MOD II Interconnection System](#)
PDF
English

Application Specification [AMPMODU Mod II And Mod IV Printed Circuit Board Connectors](#)
PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style	Receptacle
PCB Mounting Orientation	Right Angle
Row-to-Row Spacing	7.87 mm [.31 in]

Applied Pressure	High, Standard
Profile	Standard
Product Type	Connector
Applies To	Printed Circuit Board
Boss	Without
Series	AMPMODU, MOD II
Sealed	No
Connector Type	Connector Assembly

Configuration Features	Number of Positions	2
	Number of Rows	1
	Stackable	Yes

Electrical Characteristics	Voltage (VAC)	333
	Contact Resistance (M Ω)	12
	Insulation Resistance (M Ω)	5000
	Dielectric Withstanding Voltage (VAC)	750

Contact Features	Contact Mating Area Plating Material	Gold
	Contact Mating Area Plating Thickness (μ in)	30
	Contact Shape	Square
	Contact Current Rating (A)	2
	Contact Type	Socket
	Contact Configuration	Short Point
	Solder Tail Contact Plating Material	Tin-Lead over Nickel
	Contact Layout	Inline
	Solder Tail Contact Plating Thickness (μ in)	50
	Contact Base Material	Phosphor Bronze

Termination Features	Termination Method to PC Board	Through Hole - Solder
	Termination Post Length	2.92 mm [.115 in]

Mechanical Attachment	PCB Mount Retention	Without
-----------------------	---------------------	----------------

Housing Features	Centerline	2.54 mm [.1 in]
	Housing Material	Polyester - GF
	Housing Entry Style	Closed Entry, Side





Dimensions	Height	3.47 mm [.136 in]
	PCB Thickness (Recommended)	1.4 – 2.4 mm [.055 – .094 in]
	Tail Length (mm)	2.92
Usage Conditions	Operating Temperature Range (°C)	-65 – 105
	High Temperature Compatible	Yes
Operation/Application	Assembly Process Feature	Board Standoff
	For Use With	Mates with Headers
Industry Standards	UL Flammability Rating	UL 94V-0
	MIL-C-55032	No
	Approved Standards	CSA LR7189, UL E28476
Packaging Features	Packaging Method	Tube, Tube/Box
	Packaging Quantity	110
Other	Comment	TE recommends mating gold or duplex plated headers with duplex plated receptacle assemblies.

Product Compliance

[Statement of Compliance](#)
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

CUSTOMERS ALSO BOUGHT

<p>TERMINAL BLOCK HEADERS & RECEPTACLES</p>  <p>6 POS TERMI-BLOK PLUG C. VITI 284511-6</p> <p>Save to List Find Similar Products</p>	<p>USB CONNECTORS</p>  <p>USB, RCPT ASS'Y, V/T, A TYPE, 1734366-1</p> <p>Save to List Find Similar Products</p>	<p>TERMINAL BLOCK HEADERS & RECEPTACLES</p>  <p>6 POS TERMI-BLOK 900 SF 3, 81 m 284541-6</p> <p>Save to List Find Similar Products</p>	<p>MULTIPLE CONFIGURATION PCB HEADERS & RECEPTACLES</p>  <p>03 MODII HDR SRST SHRD .100CL 103414-1</p> <p>Save to List Find Similar Products</p>
-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[535676-1](#)