

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2021

© COPYRIGHT 2021 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER E.O. P17113	24JAN2001	-	RDR
C		REVISED PER E.O. P17413	17OCT2001	-	RDR
C1		REVISED PER PCN E-21-001566	11FEB2021	MK	IG
C2		REVISED PER PCN-23-189980	16OCT2023	GB	CB

Technical drawing showing front and side views of a metal clip/mounting bracket. Dimensions are provided in inches and millimeters.

Front View Dimensions:

- Total length: $2.586 \pm .050$ [65.7 ± 1.27]
- Distance from left edge to first hole: $.825$ [20.96]
- Distance between holes: $.595$ [15.11]
- Distance from right edge to second hole: $.605$ [15.37]
- Distance from left edge to center of first hole: $.275$ [6.99]
- Distance from left edge to center of second hole: $.450$ [11.44]
- Height of the main body: $.908$ [23.06]
- Surface finish: $003-12$
- Surface texture symbol: $\triangle 2$

Side View Dimensions:

- Thickness of the main body: $.040$ [1.02]
- Distance from left edge to start of clip: 1.180 [29.97]
- Distance from left edge to end of clip: 1.680 [42.67]
- Height of the clip: $.500$ [12.7]
- Height of the main body: $.632$ [16.06]

Isometric view of the metal clip/mounting bracket. Dimensions are provided in inches and millimeters.

- Height of the clip: $.455 \pm .010$ [11.56 ± 0.25]

3D perspective view of the metal clip/mounting bracket. Part number $003-12$ is visible.

3D VIEW

(C2) 3. THIS PART MATES WITH ALL DT (EXCEPT FOR 8P), DTM, DTP, DTHD RECEPTACLES OR OTHER PARTS WITH THE CLIP RETENTION FEATURE.

$\triangle 2$ PART INFORMATION.

PART NUMBER	MATERIAL	HOLE DIAMETER
1027-003-1200	STAINLESS STEEL	11MM [.433 IN]
1027-004-1200	STEEL-ZINC PLATE	13MM [.512 IN]
1027-005-1200	STAINLESS STEEL	13MM [.512 IN]

$\triangle 1$ ALL PART NUMBERS ARE IN ACCORDANCE WITH RoHS STANDARDS.

NOTES:

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		NAME	
INCH [mm]		0 PLC ±-		R REED		TE Connectivity	
		1 PLC ±-		17SEP2001		METAL CLIP/MOUNTING BRACKET	
		2 PLC ±-		PRODUCT SPEC		DT/DTM/DTP/DTHD	
		3 PLC ±.025 [0.63]		APPLICATION SPEC		-	
		4 PLC ±-		114-151009		SIZE	
		ANGLES ±°30'0"		WEIGHT		CAGE CODE	
		FINISH		10.2 g		DRAWING NO	
$\triangle 2$		$\triangle 1$		CUSTOMER DRAWING		RESTRICTED TO	
				SCALE		SHEET	
				2:1		1 OF 1	
				REV		C2	

1470-19 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1027-003-1200](#)