




































































































































REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

		3.984	3.900	39	80	9-103795-0
		3.884	3.800	38	78	8-103795-9
		3.784	3.700	37	76	8-103795-8
		3.684	3.600	36	74	8-103795-7
		3.584	3.500	35	72	8-103795-6
		3.484	3.400	34	70	8-103795-5
		3.284	3.300	33	68	8-103795-4
		3.284	3.200	32	66	8-103795-3
		3.184	3.100	31	64	8-103795-2
		3.084	3.000	30	62	8-103795-1
		2.984	2.900	29	60	8-103795-0
		2.884	2.800	28	58	7-103795-9
		2.784	2.700	27	56	7-103795-8
		2.684	2.600	26	54	7-103795-7
		2.584	2.500	25	52	7-103795-6
		2.484	2.400	24	50	7-103795-5
		2.384	2.300	23	48	7-103795-4
		2.284	2.200	22	46	7-103795-3
		2.184	2.100	21	44	7-103795-2
		2.084	2.000	20	42	7-103795-1
		1.984	1.900	19	40	7-103795-0
		1.884	1.800	18	38	6-103795-9
		1.784	1.700	17	36	6-103795-8
		1.684	1.600	16	34	6-103795-7
		1.584	1.500	15	32	6-103795-6
		1.484	1.400	14	30	6-103795-5
		1.384	1.300	13	28	6-103795-4
		1.284	1.200	12	26	6-103795-3
		1.184	1.100	11	24	6-103795-2
		1.084	1.000	10	22	6-103795-1
		.984	.900	9	20	6-103795-0
		.884	.800	8	18	5-103795-9
		.784	.700	7	16	5-103795-8
		.684	.600	6	14	5-103795-7
		.584	.500	5	12	5-103795-6
		.484	.400	4	10	5-103795-5
		.384	.300	3	8	5-103795-4
		.284	.200	2	6	5-103795-3
		.184	.100	1	4	5-103795-2
		.084	—	—	2	5-103795-1
REMARKS	PLATING	C	B	A	NO OF POS	ASSEMBLY PART NUMBER

SUPERSEDED			.384	.300	3	8	4-103795-1
OBSOLETE			3.984	3.900	39	80	4-103795-0
 OBSOLETE			3.884	3.800	38	78	3-103795-9
			3.784	3.700	37	76	3-103795-8
			3.684	3.600	36	74	3-103795-7
			3.584	3.500	35	72	3-103795-6
			3.484	3.400	34	70	3-103795-5
			3.284	3.300	33	68	3-103795-4
			3.284	3.200	32	66	3-103795-3
			3.184	3.100	31	64	3-103795-2
			3.084	3.000	30	62	3-103795-1
			2.984	2.900	29	60	3-103795-0
			2.884	2.800	28	58	2-103795-9
			2.784	2.700	27	56	2-103795-8
			2.684	2.600	26	54	2-103795-7
			2.584	2.500	25	52	2-103795-6
			2.484	2.400	24	50	2-103795-5
			2.384	2.300	23	48	2-103795-4
			2.284	2.200	22	46	2-103795-3
			2.184	2.100	21	44	2-103795-2
			2.084	2.000	20	42	2-103795-1
			1.984	1.900	19	40	2-103795-0
			1.884	1.800	18	38	1-103795-9
	SUPERSEDED		1.784	1.700	17	36	1-103795-8
 OBSOLETE			1.684	1.600	16	34	1-103795-7
			1.584	1.500	15	32	1-103795-6
			1.484	1.400	14	30	1-103795-5
			1.384	1.300	13	28	1-103795-4
OBSOLETE			1.284	1.200	12	26	1-103795-3
OBSOLETE			1.184	1.100	11	24	1-103795-2
	OBSOLETE		1.084	1.000	10	22	1-103795-1
	OBSOLETE		.984	.900	9	20	1-103795-0
OBSOLETE			.884	.800	8	18	103795-9
			.784	.700	7	16	103795-8
	 OBSOLETE		.684	.600	6	14	103795-7
			.584	.500	5	12	103795-6
			.484	.400	4	10	103795-5
SUPERSEDED			.384	.300	3	8	103795-4
 OBSOLETE			.284	.200	2	6	103795-3
			.184	.100	1	4	103795-2
			.084	—	—	2	103795-1
	REMARKS	PLATING	C	B	A	NO OF POS	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. D. RINGLEY 30JUL85	 TE Connectivity Ltd.												
DIMENSIONS: INCHES		CHK J. GESFORD 27AUG03													
		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME											
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH		APVD J. GESFORD 27AUG03		PRODUCT SPEC									
MATERIAL -		SEE TABLE		APPLICATION SPEC -		WEIGHT -		SIZE A2		CAGE CODE 00779		DRAWING NO C=103795		RESTRICTED TO -	
CUSTOMER DRAWING										SCALE 1:1		SHEET 2 of 2		REV M2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-103795-0](#)