






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E I	REVISED PER ECR-22-162100	23DEC2022	C.C	R.B
	F	REVISED PER ECR-23-171985	12APR2023	C.C	R.B
	G	Obsolete 2-1939758-1	29APR2024	R.W	R.B




△. MATERIAL: GLASS FILED THERMO PLASTIC
POLYESTER(94V-0), COLOR: BLACK

2. THE KEYING ARRANGEMENT OF "Y" IS
SYMMETRIC WITH "X".
3. THE SHAPE, SIZE AND POSITION
OF THE CHARACTER SHOW THE OUTLINE.
THEY DON'T SHOW DETAILS.










e	16	Y	15	30.0	32.9	34.6	12.8	26.4	2-1939758-3
	16	X	15	30.0	32.9	34.6	12.8	26.4	1-1939758-3
	14	Y	13	26.0	28.9	30.6	12.8	26.4	2-1939758-2
	14	X	13	26.0	28.9	30.6	12.8	26.4	1-1939758-2
	12	Y	11	22.0	24.9	26.6	6.8	14.4	2-1939758-1
	12	X	11	22.0	24.9	26.6	6.8	14.4	1-1939758-1
	10	Y	9	18.0	20.9	22.6	6.8	14.4	2-1939758-0
	10	X	9	18.0	20.9	22.6	6.8	14.4	1-1939758-0
	8	Y	7	14.0	16.9	18.6	6.8	14.4	2-1939758-8
	8	X	7	14.0	16.9	18.6	6.8	14.4	1-1939758-8
	4	Y	3	6.0	8.9	10.6	3.6	-	2-1939758-4
	4	X	3	6.0	8.9	10.6	3.6	-	1-1939758-4
POS	KEY	n	A	B	C	D	E	PART NO	



IOPOS(X-KEY) : 1-1939758-0

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. MAEBASHI 30 JUL 2007		 TE Connectivity	
		CHK T. KUDO 30 JUL 2007			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. MITSUGI 30 JUL 2007		NAME DYNAMIC DII00S 2.0mmPITCH	
	0 PLC ±-	PRODUCT SPEC		REC HSG	
	1 PLC ±0.3	108-78268, 78298		2-16POS	
	2 PLC ±-	APPLICATION SPEC		SIZE	
	3 PLC ±-	114-5377		CAGE CODE	
	4 PLC ±-			DRAWING NO	
	ANGLES ±3°	WEIGHT		RESTRICTED TO	
MATERIAL	FINISH	A3		C-1939758	
	-	CUSTOMER DRAWING		SCALE	
	-			SHEET	
				OF	
				REV	
				G	


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




4POS(X-KEY) : 1-1939758-4

8POS(X-KEY) : 1-1939758-8


16POS(X-KEY) : 1-1939758-3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. MAEBASHI 30JUL2007	 TE Connectivity DYNAMIC D1100S 2.0mmPITCH REC HSG 2-16POS		
DIMENSIONS: mm		CHK T. KUDO 30JUL2007			
		APVD D. MITSUGI 30JUL2007			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-78268,78298			
MATERIAL		APPLICATION SPEC 114-5377	NAME	SIZE	CAGE CODE
FINISH		WEIGHT	DYNAMIC D1100S 2.0mmPITCH REC HSG 2-16POS	A3	-
-		CUSTOMER DRAWING	DRAWING NO	1939758	RESTRICTED TO
-		SCALE 5:1	SHEET 2 OF 3	REV G	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



12POS(X-KEY) : 1-1939758-1



14POS(X-KEY) : 1-1939758-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. MAEBASHI	30JUL2007	 TE Connectivity			
DIMENSIONS: mm		CHK T. KUDO	30JUL2007	NAME DYNAMIC D1100S 2.0mmPITCH REC HSG 2-16POS			
		APVD D. MITSUGI	30JUL2007				
		PRODUCT SPEC 108-78268,78298					
		APPLICATION SPEC 114-5377		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL		FINISH		A3	-	C-1939758	-
-		-					
CUSTOMER DRAWING				SCALE	SHEET		REV
				5:1	3 OF 3		G

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1939758-1](#)