



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G1	REVISED PER ECN-24-262187	22APR2024	MM	LR



AS SUPPLIED



AFTER UNRESTRICTED RECOVERY

TABLE OF DIMENSIONS

PART NUMBER	H		J & K		P	R	S	T	U	W	C°		WEIGHT REF
	MIN	MAX	MIN	MAX	±10%	±10%	±10%	±10%	±10%	±20%	±10°	±5°	
	a	b	a	b	b	b	b	b	b	b	a	b	
341A015	1.12 [28,4]	.53 [13,5]	1.06 [26,9]	.53 [13,5]	5.91 [150,1]	3.16 [80,3]	2.76 [70,1]	1.53 [38,9]	1.50 [38,1]	.10 [2,5]	15°	45°	.270 [122,5]

TE Connectivity. All Rights Reserved.
2024



DIMENSIONS: INCHES	DWN M MAZARIEGOS 22APR2024	MATERIAL —		FINISH —			
	CHK C LIMA 22APR2024	TE Connectivity					
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	APVD L RODRIGUEZ 22APR2024	NAME Transition, 45 Degrees Side Breakout					
	PRODUCT SPEC —						
	APPLICATION SPEC —	SIZE A4			RESTRICTED TO —		
	WEIGHT 0	CAGE CODE 06090					
	DRAWING NO C-341A015			SCALE DNS			
	CUSTOMER DRAWING						
		SHEET 1 OF 2		REV G1			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

COMPATIBILITY CHART				
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
-3	Polyolefin, Semi-rigid	RT-301	/42; /86; /180	S1017; S1048; S1030
-4	Polyolefin, Flexible	RT-1304	/42; /86; /180	S1017; S1048; S1030
-12	Fluoroelastomer, Flexible	RT-1312	N/A	N/A
-25	Elastomer, Fluid Resistant	RW-2070	/42; /86; /225	S1017; S1048; S1206
-100	Polyolefin, semi-flexible Zerohal	RW-2082	/86; /180	S1048; S1030

ORDERING INFORMATION

341A015

-XX

-XX

/XXX

BASE PART NUMBER

MATERIAL DASH NUMBER

-3 POLYOLEFIN, SEMI RIGID (RT-301)

-4 POLYOLEFIN, FLEXIBLE (RT-1304)

-5 ELASTOMER, FLEXIBLE (RT-501)

-6 SILICONE (RT-602)

-12 FLUORO ELASTOMER, FLEXIBLE (RT-1312)

-25 ELASTOMER, FLUID RESISTANT (RT-1325)

-100 POLYOLEFIN, SEMI-FLEXIBLE ZEROHAL (RT-1323)

MODIFICATION NUMBER

ADHESIVE SLASH NUMBER

(SEE COMPATIBILITY CHART BELOW)

NOTES

1. ALL DIMENSIONS ARE IN

INCHES


[MILLIMETERS]
2. DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:

a - AS SUPPLIED

b - AFTER UNRESTRICTED RECOVERY
3. COATING (ADHESIVE): IS OPTIONAL
AS SUPPLIED DIMENSIONS APPEARING
IN TABLE ARE FOR UNCOATED PARTS.
WHEN COATING IS ADDED, ENTRY
DIAMETER WILL BE REDUCED BY .06 MAX.
4. MOLDING PORTS ARE OPTIONAL.
WHEN -00 MODIFICATION NUMBER
IS SPECIFIED MOLDING PORTS WILL BE
LOCATED AS SHOWN.
4. WEIGHT SHOWN IN TABLE OF DIMENSIONS
IS BASED ON POLYOLEFIN PART.

TE Connectivity. All Rights Reserved.
2024



DIMENSIONS: INCHES	DWN	22APR2024	MATERIAL	-	FINISH	-
	CHK	-	TE Connectivity			
	APVD	-				
	PRODUCT SPEC	-	NAME			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPLICATION SPEC	-	SIZE			
	WEIGHT	0.000000	A4	00779	C- 341A015	RESTRICTED TO
						-
0 PLC ± -	CUSTOMER DRAWING					
1 PLC ± -						
2 PLC ± -	SCALE DNS					
3 PLC ± -						
4 PLC ± -	SHEET 2 OF 2					
ANGLES ± -						
	REV G1					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[341A015-3-00-0](#) [341A015-3/42-0](#) [341A015-25-0](#) [341A015-4-0](#) [341A015-4/86-0](#) [341A015-5-0](#) [341A015-100/86-0](#)
[813453N002](#)