






LOC PROJECT		REV		REVISIONS		DATE	DWN	APVD
A1	-	P	LTR	ÄNDERUNGEN	DESCRIPTION			
			-	SEE SHEET 1		-	-	-


4 polig/POS.




6 polig/POS.




8 polig/POS.




10 polig/POS.




12 polig/POS.




14 polig/POS.




9.78




11.58




13.38










15.18



16.98






18.78



		Size ISO 14405			
		TOLERANCING ISO 8015 TOLERIERUNG ISO 8015			
DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).					
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	M. Stein	23MAR2016	
DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).		CHK	C.Boemmel	23MAR2016	
DIMENSIONS: MASSENHEITEN: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLE DIMENSIONEN		APVD	NAME
		0 PLC ± 1 PLC ± DIN 2 PLC ±16742-TG6 3 PLC ± 4 PLC ± ANGLES/WINKEL ±2°		4-22 pol., NanoMQS, Buchsengehaeuse 4-22 POS., NanoMQS, REC. HOUSING	
PRODUCT SPEC PRODUKTSPEZ. 108-94288-0		APPLICATION SPEC VERARBEITUNGSSPEZ. 114-94033		SIZE	CASE CODE
DRAWING NO. ZEICHNUNGS-NR. A1 00779		©=2303280		RESTRICTED TO NUR FÜR	
MATERIAL SEE SHEET 1 siehe Blatt 1		FINISH/SCHLACKE/FARBE SEE SHEET 1 siehe Blatt 1		- 	

TE TE Connectivity

4-22 pol., NanoMQS, Buchsengehaeuse
4-22 POS., NanoMQS, REC. HOUSING

4805 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2302475-1](#)