

D

C

B



A

D

C

B







A



SINGLE LATCH DETAIL FOR
1-2323750-2 THRU 1-2323750-6

NOTES:

- 1 MATERIAL:
HOUSING: NYLON 66, UL94V-0, COLOR NATURAL
TERMINAL: COPPER ALLOY, 2µm MIN TIN OVERALL
- 2 RECOMMENDED MATING PART: [1]-2323743-[1]
- 3 COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT)



2-2323750-0 SHOWN

1.25	2	47.50	52.89	40	4-2323750-0
0.00	2	45.00	50.39	38	3-2323750-8
1.25	2	42.50	47.89	36	3-2323750-6
0.00	2	40.00	45.39	34	3-2323750-4
1.25	2	37.50	42.89	32	3-2323750-2
0.00	2	35.00	40.39	30	3-2323750-0
1.25	2	32.50	37.89	28	2-2323750-8
0.00	2	30.00	35.39	26	2-2323750-6
1.25	2	27.50	32.89	24	2-2323750-4
0.00	2	25.00	30.39	22	2-2323750-2
1.25	2	22.50	27.89	20	2-2323750-0
0.00	2	20.00	25.39	18	1-2323750-8
1.25	1	17.50	22.89	16	1-2323750-6
0.00	1	15.00	20.39	14	1-2323750-4
1.25	1	12.50	17.89	12	1-2323750-2
0.00	1	10.00	15.39	10	1-2323750-0
1.25	1	7.50	12.89	8	2323750-8
DIM M	NO. OF LATCH CUT-OUTS	DIM F	DIM L	NO. OF POSITION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±0.25
3 PLC ±
4 PLC ±
ANGLES ±5°
FINISH

APVD
DANIEL ZHANG
27AUG2018

PRODUCT SPEC
108-106357
APPLICATION SPEC
114-13315
WEIGHT
-

CUSTOMER DRAWING

DWN
WARREN HUO
26AUG2018

CHK
DANIEL ZHANG
27AUG2018

APVD
DANIEL ZHANG
27AUG2018

TE Connectivity

NAME
HEADER ASSEMBLY, EP2.5 DUAL ROW
RIGHT ANGLE, GWT

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2323750

RESTRICTED TO
-

SCALE
N/A

SHEET
1

OF
1

REV
A

1471-9 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2323750-6](#)