







DRAWN	B.VESA		DATE	08/02/2017	 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER:			95A SERIES			 Polamco 	
SALES APPR			DATE	08/02/2017		TITLE:			BRAID TRAP BACKSHELL				
DESIGN APPR	K.SHEPPARD		DATE	09/02/2017		UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°	ASSY USED ON: MIL-C-26482 SERIES II, MIL-C-83723 SERIES I & III						
PROD APPR													
QUAL APPR													
ISSUE	REV.	DCR		6474	SEE PART NUMBER BREAKDOWN	THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.			POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP		SHT	DRAWING NO: P11329	
2					FINISH SEE PART NUMBER BREAKDOWN						1		
NCAGE CODE U5792				WEIGHT	---								

TABLE 1

SHELL SIZE	A THREAD	ØB MAX	ØT MIN	C ±0,5	D ±0,5	D PLAIN NUT ±0,5	E MAX	F ±0,5	F PLAIN NUT ±0,5	K ±0,5
08	1/2-20 UNF	15,6	6,5	16,8	24,0	20,0	24,7	30,5	26,5	17,5
10	5/8-24 UNEF	18,6	9,2	17,0	24,7	20,7	26,7	32,2	28,2	17,8
12	3/4-20 UNEF	21,7	12,7	17,5	25,1	21,1	29,2	33,0	29,0	18,7
14	7/8-20 UNEF	24,9	14,6	18,3	26,0	22,0	30,7	34,4	30,4	19,0
16	1-20 UNEF	28,2	17,7	19,2	26,8	22,8	34,2	36,9	32,9	21,0
18	1 1/16-18 UNEF	30,9	19,7	19,4	27,3	23,3	37,2	36,9	32,9	23,5
20	1 3/16-18 UNEF	34,1	22,9	20,3	28,2	24,2	42,2	38,5	34,5	27,0
22	1 5/16-18 UNEF	37,3	26,1	20,5	28,5	24,5	44,2	40,2	36,2	27,0
24	1 7/16-18 UNEF	40,4	29,0	22,0	29,4	25,4	45,2	41,6	37,6	27,0

TABLE 2

ENTRY SIZE	ØG MIN	W MAX	ØH MAX	J MAX	M ±0,5
03	4,7	17,3	15,2	13,7	5,8
04	6,3	18,9	15,2	13,7	5,7
05	7,9	20,5	16,8	13,7	6,8
06	9,5	22,1	18,4	13,7	6,9
07	11,1	23,6	20,0	13,7	8,1
08	12,7	25,1	21,6	16,7	8,5
09	14,2	26,8	23,2	16,7	9,7
10	15,8	28,4	24,8	16,7	10,4
11	17,4	30,1	26,4	19,7	11,5
12	19,0	31,6	27,9	19,7	11,4
13	20,6	33,1	29,5	19,7	14,0
14	22,2	34,8	31,1	22,7	15,4
15	23,8	36,5	32,7	22,7	16,8
16	25,4	37,9	34,3	22,7	17,3
17	27,0	39,5	35,9	22,7	18,8
18	28,6	41,1	37,5	22,7	19,5
19	30,2	42,7	39,3	24,2	25,9
20	31,8	44,3	40,6	24,2	23,4
21	33,3	45,8	42,2	24,2	24,8
22	35,0	N/A	43,8	N/A	N/A
23	36,5	47,4	45,4	24,2	25,4
24	38,1	50,9	47,0	24,2	27,4

TABLE 3

CODE	FINISH
C	ELECTROLESS NICKEL
B	CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
ZB	ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
ZN	ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL

LIST NOT EXHAUSTIVE, FOR COMPREHENSIVE LIST AND SPECS, SEE WEBSITE

95A1-16-08-1-C-CC-L50

SERIES _____

CONNECTOR INTERFACE _____

ANGLE _____

SHELL SIZE (TABLE 1) _____

ENTRY SIZE (TABLE 2) _____

MATERIAL _____

ALUMINIUM ALLOY _____

FINISH (TABLE 3) _____

CABLE CLAMP OPTION _____

OMIT FOR PLAIN NUT _____

LENGTH OPTION IN MM (STRAIGHT ONLY) _____

OMIT FOR STANDARD - 28 mm _____

DRAWN	B.VESA		DATE	08/02/2017	 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER:	95A SERIES			 Polamco	
SALES APPR			DATE	08/02/2017		TITLE:	BRAID TRAP BACKSHELL				
DESIGN APPR	K.SHEPPARD		DATE	09/02/2017		UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°	ASSY USED ON: MIL-C-26482 SERIES II, MIL-C-83723 SERIES I & III				
PROD APPR											
QUAL APPR					MATERIAL						
ISSUE	REV.	DCR			SEE PART NUMBER BREAKDOWN						
2		6474			FINISH						
NCAGE CODE U5792			WEIGHT	---	SEE PART NUMBER BREAKDOWN	THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.		POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP	SHT	2	DRAWING NO: P11329

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[95A3-14-09-1-B](#)