

printed on 8 May 2024 17:17 (China Standard Time) from TE343936



© 2023 TE Connectivity. All Rights Reserved.

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	16OCT2023	AD	CW
	A1	ECR-24-208147	08MAY2024	AD	CW

NOTES:
1. TECHNICAL CHARACTERISTICS:
CONTACT MATERIAL: BRASS ALLOY
SURFACE TREATMENT: GOLD PLATING
CONTACT RESISTANCE: $\leq 15m\Omega$
OPERATION TEMPERATURE: $-40\sim+125^{\circ}C$
DIGITAL CRIMPING TOOL:
TE PART NO.: C0-0235-000-000
LOCATOR FOR DIGITAL CRIMPING TOOL:
TE PART NO.: C0-0265-000-000

注释:
1. 技术参数:
针件材料: 铜合金
表面处理: 镀金
接触电阻: $\leq 15m\Omega$
工作温度: $-40\sim+125^{\circ}C$
数码压接工具:
TE料号: C0-0235-000-000
数码压接工具的定位器:
TE料号: C0-0265-000-000



T2400011002-000	ETH-CP-0.6	ETHERNET PIN CONTACT $\varnothing 0.6MM$, GOLD PLATED, CRIMP 以太网公端子 $\varnothing 0.6$, 镀金, 压接
PART NUMBER 料 号	PART DESCRIPTION 描 述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16OCT2023 Alan Dong	 TE Connectivity		
		CHK 16OCT2023 Gino Yao			
DIMENSIONS: mm		APVD 16OCT2023 Chris Wang	NAME ETHERNET PIN CONTACT CALIBER 0.6MM		
		PRODUCT SPEC 108-137683			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC \pm - 1 PLC \pm - 2 PLC \pm - 3 PLC \pm - 4 PLC \pm - ANGLES \pm -		APPLICATION SPEC 114-137683	SIZE A3		
MATERIAL -		WEIGHT 0.09 g	CAGE CODE 00779	DRAWING NO T2400011002000	RESTRICTED TO -
FINISH -		CUSTOMER DRAWING		SCALE 10:1	SHEET 1 OF 1
				REV A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2400011002-000](#)