








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	11JUL2024	RK	PSS

NOTES:

- 1.HOUSING MATERIAL:GLASS FILLED LCP(BLACK) UL94V-0(ROHS)
- 2.CONTACT:PHOSPHOR BRONZE.50 MICROINCHES MIN. OVERALL DUCTILE NICKEL UNDERPLATEWITH SELECTED (REFER P/N TABLE) MICROINCHES GOLD AT MATING INTERFACE
- 3.SHIELD:0.2mm THICKNESS WITH BRASS.
- 4.JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68 SUBPART F
- 5.THE PART IS RECOMMENDDDED FOR WAVE SOLDERING PROCESS PEAK SOLDERING TEMPERATURE IS 265±5°C ,10 SECS.
- 6.OPERATING TEMPERATURE:-40°C TO +85°C.
STORAGE TEMPERATURE:-40°C TO +85°C.




RECOMMENDED P.C.B LAYOUT
TOP VIEW (COMPONENT SIDE)
Dimensions Tolerance:
All PCB LAYOUT
Tolerances:±0.05[.002]



0.04572 μm [1.8μ"]	2489102-6
0.0762 μm [3μ"]	2489102-5
0.1524 μm [6μ"]	2489102-4
0.381 μm [15μ"]	2489102-3
0.762 μm [30μ"]	2489102-2
1.27 μm [50μ"]	2489102-1
GOLD PLATING THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAMESH KIVADER 12JUN2024	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK RAMESH KIVADER 12JUN2024	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD P.S. SATHISH 12JUN2024	PRODUCT SPEC	
0. PLC ± 0.10 1. PLC ± 0.25 2. PLC ± 0.25 3. PLC ± 0.25 4. PLC ± 0.25 ANGLES ± 2		APPLICATION SPEC		SIZE
MATERIAL		WEIGHT		CAGE CODE
-		0		DRAWING NO
-		A100779		RESTRICTED TO
-		CUSTOMER DRAWING		SCALE
-		1:1		SHEET
-		1		OF
-		2		REV
-		A		

Schematic



PARAMETER	SPECIFICATIONS
OPERATING TEMPERATURE	-40°C To +85°C
URNS RATIO	1:1±2%
OPEN CIRCUIT INDUCTANCE(OCL)	180uH MIN@100KHz/100mV With 8mA DC Bias For(CHANNEL 1,2,3,4)
INSERTION LOSS(IL)	-1.0dB MAX@1MHz-50MHz; -1.5dB MAX@50MHz-125MHz;
RETURN LOSS(RL) (Z out=100 OHM)	-18dB MIN@1MHz-40MHz; -18+15LOG (f/40MHz)dB MIN@40MHz-250MHz;
CROSSTALK (ADJACENT CHANNELS)	-35dB MIN@1MHz-40MHz; -35+15LOG (f/40MHz)dB MIN@40MHz-125MHz;
COMMON MODE REJECTION RATIO(CMRR)	-30dB MIN@1MHz-200MHz;
COMMON TO DIFFERENTIAL MODE REJECTION(REF)	-35dB MIN@1MHz-125MHz;
HI-POT	2250 VDC@60 SECONDS

LED SPECIFICATION			
STANDARD LED	WAVELENGTH	Farward V(max)	TYP
GREEN	570nm	2.4V	2.2V
YELLOW	590nm	2.5V	2.1V
ORANGE	605nm	2.5V	2.1V

*WITH A FORWARD CURRENT OF 20mA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2489102-2](#)